



225 Full Circle® Clamp Single Band



Nominal Size Inches	O.D. Range Inches	Width Inches	With Alloy Bolts And Nuts		With S.S. Bolts And Nuts		Wt. Each Lbs.
			Catalog Number	List Price	Catalog Number	List Price	
2	2.25-2.50	7 1/2	225-10022507-000	\$96.51	225-10022507-001	\$124.62	8.4
		10	225-10022510-000	145.08	225-10022510-001	175.80	11.5
		12 1/2	225-10022512-000	171.71	225-10022512-001	204.28	14.1
		15	225-10022515-000	198.11	225-10022515-001	231.78	17.3
2	2.35-2.63	7 1/2	225-10023807-000	98.62	225-10023807-001	126.71	8.8
		10	225-10023810-000	148.62	225-10023810-001	179.34	11.8
		12 1/2	225-10023812-000	175.05	225-10023812-001	206.91	14.6
		15	225-10023815-000	201.35	225-10023815-001	235.04	17.5
2 1/2	2.70-3.00	7 1/2	225-10027507-000	107.10	225-10027507-001	135.04	8.8
		10	225-10027510-000	158.61	225-10027510-001	189.43	11.8
		12 1/2	225-10027512-000	184.41	225-10027512-001	215.99	14.6
		15	225-10027515-000	215.76	225-10027515-001	248.27	17.5
3	3.36-3.60	7 1/2	225-10033607-000	114.84	225-10033607-001	140.88	9.2
		10	225-10033610-000	162.49	225-10033610-001	193.25	12.4
		12 1/2	225-10033612-000	190.53	225-10033612-001	221.85	15.3
		15	225-10033615-000	226.18	225-10033615-001	255.73	18.1
3	3.46-3.70	7 1/2	225-10035007-000	117.18	225-10035007-001	147.45	9.2
		10	225-10035010-000	165.82	225-10035010-001	198.36	12.4
		12 1/2	225-10035012-000	194.42	225-10035012-001	227.85	15.3
		15	225-10035015-000	230.81	225-10035015-001	263.16	18.1
3	3.73-4.00	7 1/2	225-10037507-000	120.40	225-10037507-001	150.17	9.2
		10	225-10037510-000	171.62	225-10037510-001	204.28	12.4
		12 1/2	225-10037512-000	200.08	225-10037512-001	237.09	15.3
		15	225-10037515-000	238.35	225-10037515-001	273.08	18.1
4	4.32-4.60	7 1/2	225-10043207-000	122.27	225-10043207-001	153.89	9.2
		10	225-10043210-000	175.09	225-10043210-001	209.09	12.4
		12 1/2	225-10043212-000	208.50	225-10043212-001	244.57	15.3
		15	225-10043215-000	246.46	225-10043215-001	279.07	18.1
4	4.45-4.73	7 1/2	225-10045007-000	128.70	225-10045007-001	159.40	9.6
		10	225-10045010-000	179.33	225-10045010-001	215.01	13.0
		12 1/2	225-10045012-000	217.30	225-10045012-001	252.25	15.9
		15	225-10045015-000	253.36	225-10045015-001	287.99	18.9
4	4.74-5.14	7 1/2	225-10048007-000	133.22	225-10048007-001	170.40	10.5
		10	225-10048010-000	180.14	225-10048010-001	234.54	14.5
		12 1/2	225-10048012-000	218.32	225-10048012-001	275.46	17.5
		15	225-10048015-000	263.36	225-10048015-001	339.78	20.8
		20	225-10048020-000	353.70	225-10048020-001	464.98	27.9
		30	225-10048030-000	544.75	225-10048030-001	700.00	41.2



225 Full Circle® Clamp Single Band



Nominal Size Inches	O.D. Range Inches	Width Inches	With Alloy Bolts & Nuts		With S.S. Bolts & Nuts		Wt. Each Lbs.
			Catalog Number	List Price	Catalog Number	List Price	
6	6.40-6.80	7 1/2	225-10064007-000	\$150.78	225-10064007-001	\$190.31	11.6
		10	225-10064010-000	207.25	225-10064010-001	259.89	15.6
		12 1/2	225-10064012-000	242.90	225-10064012-001	309.35	19.2
		15	225-10064015-000	273.32	225-10064015-001	360.55	22.6
		20	225-10064020-000	409.21	225-10064020-001	520.79	30.6
		30	225-10064030-000	589.52	225-10064030-001	746.10	44.7
6	6.56-6.96	7 1/2	225-10066307-000	153.85	225-10066307-001	194.19	11.6
		10	225-10066310-000	211.95	225-10066310-001	265.20	15.6
		12 1/2	225-10066312-000	247.85	225-10066312-001	315.24	19.2
		15	225-10066315-000	278.91	225-10066315-001	367.90	22.6
		20	225-10066320-000	417.55	225-10066320-001	531.42	30.6
		30	225-10066330-000	601.57	225-10066330-001	761.31	44.7
6	6.84-7.24	7 1/2	225-10069007-000	157.22	225-10069007-001	198.53	11.6
		10	225-10069010-000	213.25	225-10069010-001	270.04	15.6
		12 1/2	225-10069012-000	251.47	225-10069012-001	319.34	19.3
		15	225-10069015-000	292.23	225-10069015-001	372.40	22.9
		20	225-10069020-000	423.44	225-10069020-001	536.55	30.5
		30	225-10069030-000	617.04	225-10069030-001	776.65	45.7
8	8.38-8.78	7 1/2	225-10083807-000	176.80	225-10083807-001	219.64	13.3
		10	225-10083810-000	238.15	225-10083810-001	295.42	17.2
		12 1/2	225-10083812-000	283.47	225-10083812-001	353.48	20.8
		15	225-10083815-000	338.08	225-10083815-001	418.83	24.7
		20	225-10083820-000	474.61	225-10083820-001	585.76	33.6
		30	225-10083830-000	660.83	225-10083830-001	853.41	50.4
8	8.54-8.94	7 1/2	225-10086307-000	182.28	225-10086307-001	226.44	13.3
		10	225-10086310-000	245.46	225-10086310-001	304.55	17.2
		12 1/2	225-10086312-000	292.25	225-10086312-001	364.41	20.8
		15	225-10086315-000	348.55	225-10086315-001	431.77	24.7
		20	225-10086320-000	489.30	225-10086320-001	603.90	33.6
		30	225-10086330-000	681.25	225-10086330-001	879.82	50.4
8	8.99-9.39	7 1/2	225-10090507-000	188.09	225-10090507-001	231.65	13.1
		10	225-10090510-000	248.87	225-10090510-001	307.15	17.3
		12 1/2	225-10090512-000	301.18	225-10090512-001	372.27	21.3
		15	225-10090515-000	358.89	225-10090515-001	447.10	25.3
		20	225-10090520-000	497.19	225-10090520-001	614.33	34.6
		30	225-10090530-000	699.76	225-10090530-001	895.42	50.4



225 Full Circle® Clamp Single Band



Nominal Size Inches	O.D. Range Inches	Width Inches	With Alloy Bolts & Nuts		With S.S. Bolts & Nuts		Wt. Each Lbs.
			Catalog Number	List Price	Catalog Number	List Price	
10	10.60-11.00	7 1/2	225-10106007-000	\$219.63	225-10106007-001	\$250.40	13.5
		10	225-10106010-000	293.61	225-10106010-001	347.19	17.4
		12 1/2	225-10106012-000	341.38	225-10106012-001	410.98	22.1
		15	225-10106015-000	436.81	225-10106015-001	519.66	26.2
		20	225-10106020-000	584.83	225-10106020-001	694.42	34.8
		30	225-10106030-000	873.61	225-10106030-001	1,034.65	52.2
10	10.64-11.04	7 1/2	225-10107507-000	224.12	225-10107507-001	255.50	13.9
		10	225-10107510-000	299.59	225-10107510-001	354.29	18.9
		12 1/2	225-10107512-000	348.34	225-10107512-001	419.36	23.0
		15	225-10107515-000	445.70	225-10107515-001	530.26	26.7
		20	225-10107520-000	596.77	225-10107520-001	708.58	35.9
		30	225-10107530-000	891.45	225-10107530-001	1,055.64	54.2
10	11.04-11.44	7 1/2	225-10111007-000	228.92	225-10111007-001	267.51	14.0
		10	225-10111010-000	309.30	225-10111010-001	359.11	18.7
		12 1/2	225-10111012-000	355.59	225-10111012-001	426.60	22.9
		15	225-10111015-000	448.14	225-10111015-001	539.83	27.6
		20	225-10111020-000	599.14	225-10111020-001	727.90	36.6
		30	225-10111030-000	910.89	225-10111030-001	1,079.75	54.9
12	12.60-13.00	7 1/2	225-10126007-000	251.75	225-10126007-001	293.79	15.6
		10	225-10126010-000	334.84	225-10126010-001	392.45	20.2
		12 1/2	225-10126012-000	405.16	225-10126012-001	477.04	24.9
		15	225-10126015-000	503.45	225-10126015-001	585.15	28.9
		20	225-10126020-000	664.98	225-10126020-001	777.85	39.8
		30	225-10126030-000	1,006.91	225-10126030-001	1,137.35	59.7
12	13.10-13.50	7 1/2	225-10132007-000	258.20	225-10132007-001	301.31	16.6
		10	225-10132010-000	343.41	225-10132010-001	402.50	20.7
		12 1/2	225-10132012-000	415.55	225-10132012-001	489.26	25.3
		15	225-10132015-000	516.37	225-10132015-001	600.13	29.1
		20	225-10132020-000	682.02	225-10132020-001	797.76	40.4
		30	225-10132030-000	1,032.72	225-10132030-001	1,166.51	60.6
14	14.00-14.40	7 1/2	225-10140007-000	272.83	225-10140007-001	322.99	18.8
		10	225-10140010-000	355.60	225-10140010-001	421.78	23.1
		12 1/2	225-10140012-000	433.52	225-10140012-001	515.79	28.9
		15	225-10140015-000	540.70	225-10140015-001	636.32	34.7
		20	225-10140020-000	711.21	225-10140020-001	831.52	46.2
		30	225-10140030-000	1,083.88	225-10140030-001	1,205.11	69.3

Larger clamps available upon request.