

Series 1510 Pump Bearing Frame Selection Chart – Standard Seal– T Frame Motors

SMALL BEARING FRAME									LARGE BEARING FRAME																EXTRA LARGE BEARING FRAME*					
PART NO. 185011 (Bronze Fitted) 185012 (All Iron) 185013 (All Bronze)									PART NO. 185014 (Bronze Fitted) 185015 (All Iron) 185016 (All Bronze)																PART NO. P51701 (Bronze Fitted) P51702 (All Iron)					
FRAME #	56	143T	145T	182T	184T	213T	215T	254T	213T	215T	254T	256T	284T	284TS	286T	286TS	324T	324TS	326T	326TS	364T	364TS	365T	365TS	404TS	326T	364TS	365TS	404TS	405TS
SIZE																														
1¼"AC	X	X	XX X	XX	XX	XX	XX																							
1½"AB	X	X	X	XX	XX	XX	XX																							
2"AC	X	X	XX X	XX X	XX	XX	XX	XX																						
2½"AB	X	X	X	XX X	XX X	XX	XX	XX																						
3"AB		X	X	X	X	X	X		XX	XX	XX	XX		XX		XX														
4"AC			X	X	X	X	X			XX	XX	XX		XX		XX		XX		XX										
5"A				X	X	X	X					XX		XX		XX		XX		XX		XX								
1¼"BC		X	X	X	X				XX	XX	XX	XX		XX																
1½"BB		X	X	X	X	X	X		XX	XX	XX	XX		XX		XX		XX												
2"BC			X	X	X	X	X			XX	XX	XX		XX		XX		XX		XX										
2½"BB				X	X	X	X				XX	XX		XX		XX		XX		XX		XX								
3"BB			X	X	X	X	X	X				XX		XX		XX		XX		XX		XX								
4"BC						X	X	X				X				XX		XX		XX		XX			XX		XX	XX		
5"BC						X	X	X				X	X																	
6"BC											X	X	X		X		X		X											
2"E				X	X	X	X	X							XX		XX		XX		XX		XX		XX					
3"E						X	X	X				X					XX		XX		XX		XX		XX	XX				
4"E							X	X				X	X		X		XX		XX		XX		XX		XX	XX				
5"E											X	X	X		X		X													
6"E													X		X		X		X			X								
2"G									X	X	X	X	X																	
3"G									X	X	X	X	X		X															
4"G									X	X	X	X	X		X															
5"G											X	X	X		X		X		X		X						X	X	X	
6"G															X		X		X		X			X		X		X	X	X

X FOR 1150 RPM OR 1750 RPM APPLICATIONS
 XX FOR 3450 RPM APPLICATIONS
 *USED ON 5G & 6G PUMPS WITH IMPELLER DIA. LARGER THAN 12½"

Series 1510 Pump Bearing Frame Selection Chart – Box Type – T Frame Motors

SMALL BEARING FRAME									LARGE BEARING FRAME															EXTRA LARGE BEARING FRAME*						
PART NO. P85001 (Bronze Fitted) P85001 (All Iron) P85005 (All Bronze)									PART NO. P85007 (Bronze Fitted) P85007 (All Iron) P85006 (All Bronze)															PART NO. P51705 (All Constr.)						
FRAME #	56	143T	145T	182T	184T	213T	215T	254T	213T	215T	254T	256T	284T	284TS	286T	286TS	324T	324TS	326T	326TS	364T	364TS	365T	365TS	404TS	326T	364TS	365TS	404TS	405TS
SIZE																														
1¼"AC	X	X	XX X	XX	XX	XX	XX																							
1½"AB	X	X	X	XX	XX	XX	XX																							
2"AC	X	X	XX X	XX X	XX				XX	XX	XX	XX																		
2½"AB	X	X	X	XX X	XX X				XX	XX	XX	XX																		
3"AB		X	X	X	X	X	X		XX	XX	XX	XX		XX		XX														
4"AC		X	X	X	X	X	X		XX	XX	XX	XX		XX		XX		XX		XX										
5"A				X	X	X	X					XX	XX	XX	XX		XX		XX			XX								
1¼"BC		X	X	X	X				XX	XX	XX	XX		XX																
1½"BB		X	X	X	X	X	X		XX	XX	XX	XX		XX		XX		XX												
2"BC			X	X	X	X	X			XX	XX	XX		XX		XX		XX			XX									
2½"BB				X	X	X	X				XX	XX		XX		XX		XX			XX									
3"BB			X	X	X	X	X	X				XX		XX		XX		XX			XX									
4"BC									X	X	X	X																		
5"BC									X	X	X	X	X																	
6"BC											X	X	X		X		X		X											
2"E				X	X	X	X	X								XX		XX		XX		XX		XX						
3"E						X	X	X				X						XX		XX		XX		XX		XX				
4"E							X	X				X	X		X			XX		XX		XX		XX		XX				
5"E											X	X	X		X		X													
6"E												X	X		X		X		X			X								
2"G									X	X	X	X	X																	
3"G									X	X	X	X	X		X															
4"G									X	X	X	X	X		X															
5"G											X	X	X		X		X*		X*		X*	X*				X	X	X		
6"G															X		X*		X*		X*	X*	X			X		X	X	

X FOR 1150 RPM OR 1750 RPM APPLICATIONS
 XX FOR 3450 RPM APPLICATIONS
 *USED ON 5G & 6G PUMPS WITH IMPELLER DIA. LARGER THAN 12½"