




JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



5BD

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

STAINLESS STEEL FITTED

FEATURES

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- 175 psi (12 bar) W.P. w/125# ANSI flange drilling
- 250 psi (17 bar) W.P. w/250# ANSI flange drilling (requires 1510-S)

TYPE OF SEAL


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling





JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



5BD

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

STAINLESS STEEL FITTED

FEATURES

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- 175 psi (12 bar) W.P. w/125# ANSI flange drilling
- 250 psi (17 bar) W.P. w/250# ANSI flange drilling (requires 1510-S)

TYPE OF SEAL


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling



Series e-1510 5BD Centrifugal Pump Submittal

B-880.26C



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	5" (127)	1-3/8" (35)	10-3/4" (273)
Suction	6" (152)	1-7/16" (37)	12-1/8" (308)

FLANGES ARE 125# ANSI - STANDARD
250# ANSI - AVAILABLE

DIMENSIONS - Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"S" FRAME														
213T	16 (406)	46-1/2 (1181)	39-1/8 (994)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-9/16 (116)	20-7/8 (530)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
215T	16 (406)	46-1/2 (1181)	40-5/8 (1032)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-9/16 (116)	20-7/8 (530)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
254T	16 (406)	46-1/2 (1181)	44-3/8 (1127)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-9/16 (116)	21-7/8 (556)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
"L" FRAME														
256T	16 (406)	46-1/2 (1181)	50-1/2 (1283)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	6-7/16 (164)	21-7/8 (556)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
284T	16 (406)	51-3/4 (1314)	51-1/8 (1299)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	6-7/16 (164)	23 (584)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
286T	16 (406)	51-3/4 (1314)	52-1/2 (1333)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	6-7/16 (164)	23 (584)	25 (635)	5 (127)	6 (152)	7-1/2 (190)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"L" FRAME														
213T	16 (406)	46-1/2 (1181)	45-7/8 (1165)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	6-7/16 (163)	20-7/8 (530)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
215T	16 (406)	46-1/2 (1181)	47-3/8 (1203)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	6-7/16 (163)	20-7/8 (530)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
254T	16 (406)	51-3/4 (1314)	51-1/8 (1298)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	6-7/16 (163)	21-7/8 (555)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
256T	16 (406)	51-3/4 (1314)	52-7/8 (1343)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	6-7/16 (163)	21-7/8 (555)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
284T	16 (406)	51-3/4 (1314)	53-5/8 (1362)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	6-7/16 (163)	23 (584)	25 (635)	5 (127)	6 (152)	7-1/2 (190)
286T	16 (406)	51-3/4 (1314)	55 (1397)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	6-7/16 (163)	23 (584)	25 (635)	5 (127)	6 (152)	7-1/2 (190)

Dimensions are subject to change. Not to be used for construction purposes unless certified.



Xylem Inc.
8200 N. Austin Avenue, Morton Grove, IL 60053
Phone: (847)966-3700 Fax: (847)965-8379
www.bellgossett.com
Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2016 Xylem Inc.