




<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



## 6G

### Series e-1510

**Centrifugal Pumps - Base Mounted**

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

Stainless Steel Fitted

**FEATURES**

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


**MAXIMUM WORKING PRESSURE**

- 175 psi (12 bar) W.P. w/ 125# ANSI flange drilling
- 250 psi (17 bar) W.P. w/250# ANSI flange drilling (requires 1510-S)

**TYPE OF SEAL**


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

**Note:** Equipped with NEOPRENE coupling





<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



## 6G Series e-1510

### Centrifugal Pumps - Base Mounted

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

Stainless Steel Fitted

**FEATURES**

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


**MAXIMUM WORKING PRESSURE**

- 175 psi (12 bar) W.P. w/ 125# ANSI flange drilling
- 250 psi (17 bar) W.P. w/250# ANSI flange drilling (requires 1510-S)

**TYPE OF SEAL**


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

**Note:** Equipped with NEOPRENE coupling



**Series e-1510 6G Centrifugal Pump Submittal**

**B-880.48B**



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	6" (152)	1-7/16 (37)	12-1/8 (308)
Suction	8" (203)	1-5/8 (41)	14-3/4 (375)

FLANGES ARE: 125# ANSI - STANDARD  
250# ANSI - AVAILABLE

**DIMENSIONS - Inches (mm)**

**STANDARD SEAL**


MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub>	HH	HL	HM MAX	HO	HP	Y	Z
<b>"L" FRAME</b>														
256T	24 (610)	56 (1422)	49-5/8 (1260)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	23-3/8 (594)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
284T	24 (610)	56 (1422)	50-5/8 (1286)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	24-1/2 (622)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
286T	24 (610)	56 (1422)	52-1/8 (1324)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	24-1/2 (622)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
324T	24 (610)	56 (1422)	54-1/8 (1375)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	25-5/8 (651)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
326T	24 (610)	56 (1422)	55-5/8 (1413)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	25-5/8 (651)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
364T	24 (610)	56 (1422)	57-7/8 (1470)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	26-3/4 (679)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
365T	24 (610)	56 (1422)	58-1/2 (1486)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	26-3/4 (679)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
404TS	24 (610)	56 (1422)	58-5/8 (1489)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	28-3/8 (721)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
405TS	24 (610)	56 (1422)	59-3/8 (1508)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	30 (762)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
<b>"XL" FRAME</b>														
324T	26 (660)	59-1/4 (1505)	58-7/8 (1495)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	25-1/4 (641)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
326T	26 (660)	59-1/4 (1505)	60-5/16 (1532)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	25-1/4 (641)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
364TS	26 (660)	59-1/4 (1505)	62-9/16 (1589)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	26-1/8 (663.5)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
365TS	26 (660)	59-1/4 (1505)	62-1/2 (1588)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	27-1/4 (692)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
404TS	26 (660)	59-1/4 (1505)	64-3/4 (1645)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	28-7/8 (733)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
405TS	26 (660)	59-1/4 (1505)	66-1/4 (1683)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	28-7/8 (733)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
444TS	26 (660)	59-1/4 (1505)	70-5/8 (1794)	18 (457)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	29-3/4 (756)	32 (813)	6 (152)	6-1/2 (165)	9-5/16 (237)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

At 1800 RPM operation and impeller diameters greater than 12.5", "XL" bearing frame required.

**Series e-1510 6G Centrifugal Pump Submittal**

**B-880.48B**



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	6" (152)	1-7/16 (37)	12-1/8 (308)
Suction	8" (203)	1-5/8 (41)	14-3/4 (375)

FLANGES ARE: 125# ANSI - STANDARD  
250# ANSI - AVAILABLE

**DIMENSIONS - Inches (mm)**

**STUFFING BOX**

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub>	HH	HL	HM MAX	HO	HP	Y	Z
<b>"L" FRAME</b>														
256T	24 (610)	56 (1422)	52 (1321)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	23-3/8 (594)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
284T	24 (610)	56 (1422)	53 (1346)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	24-1/2 (622)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
286T	24 (610)	56 (1422)	54-1/2 (1384)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	24-1/2 (622)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
324T	24 (610)	56 (1422)	56-1/2 (1435)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	25-5/8 (651)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
326T	24 (610)	56 (1422)	58 (1473)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	25-5/8 (651)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
364T	24 (610)	56 (1422)	60-1/4 (1530)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	26-3/4 (679)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
365T	24 (610)	56 (1422)	60-7/8 (1546)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	26-3/4 (679)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
404TS	24 (610)	56 (1422)	61 (1549)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	28-3/8 (721)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
405TS	24 (610)	56 (1422)	62 (1575)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	6-1/4 (159)	30 (762)	30-1/2 (775)	6 (152)	6-1/2 (165)	9-5/16 (237)
<b>"XL" FRAME</b>														
324T	26 (660)	59-1/4 (1505)	62-3/8 (1584)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	25-1/4 (641)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
326T	26 (660)	59-1/4 (1505)	62-3/8 (1584)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	25-1/4 (641)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
364TS	26 (660)	59-1/4 (1505)	62-3/4 (1594)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	26-1/8 (664)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
365TS	26 (660)	59-1/4 (1505)	64-3/4 (1645)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	27-1/4 (692)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
404TS	26 (660)	59-1/4 (1505)	67 (1702)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	28-7/8 (733)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
405TS	26 (660)	59-1/4 (1505)	68-1/2 (1740)	17 (432)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	28-7/8 (733)	31 (787)	6 (152)	6-1/2 (165)	9-5/16 (237)
444TS	26 (660)	59-1/4 (1505)	72-3/4 (1848)	18 (457)	23-1/2 (597)	47-1/4 (1200)	23-5/8 (600)	1 (25)	6-1/2 (165)	29-3/4 (756)	32 (813)	6 (152)	6-1/2 (165)	9-5/16 (237)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

At 1800 RPM operation and impeller diameters greater than 12.5", "XL" bearing frame required.



Xylem Inc.  
8200 N. Austin Avenue, Morton Grove, IL 60053  
Phone: (847)966-3700 Fax: (847)965-8379  
www.bellgossett.com  
Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.  
© 2016 Xylem Inc.