

Flojet Duplex Series

Model number	2100-12	2100-740	2100-750	2100-916	2100-919	2125-030A	2125-507	2125-230
Flow rate	2.3 GPM (8.9 LPM)	2.3 GPM (8.9 LPM)	2.3 GPM (8.9 LPM)	1.4 GPM (5.3 LPM)	1.3 GPM (4.9 LPM)	1 oz./sec. (29.5 ml/sec.)	0.5 oz./sec. (14.8 ml/sec.)	1 oz./sec. (29.5 ml/sec.)
Max. pressure / pressure switch setting	45 psi (3.2 bar)	45 psi (3.2 bar)	45 psi (3.2 bar)	45 psi (3.2 bar)	45 psi (3.2 bar)	50 psi (3.4 bar) max.	90 psi (6.2 bar) max.	50 psi (3.4 bar) max.
Voltage	12 V DC	12 V DC	12 V DC	12 V DC	12 V DC	115 VAC	115 VAC	115 VAC