



TYPICAL
GUIDE RAIL
BASIN KIT

FEATURES


- Simplex and Duplex Basin Assemblies in 1.25" and 2.00" discharge sizes for the for the 2HP models of the AGS, RGS and 1GD pump families
- Heavy duty fiberglass basin for in-ground installations
- Multiple basin sizes to accommodate a variety of grinder applications
- Unirail with brass quick disconnects for ease of installation and easy pump removal
- Axial and radial grinding designs proven to handle the challenges of the modern wastewater stream

Grinder Packages


FOR 2 HP MODELS



GUIDE RAIL EQUIPPED BASINS IN SIMPLEX & DUPLEX CONFIGURATIONS



NON-GUIDE RAIL EQUIPPED BASINS IN SIMPLEX & DUPLEX CONFIGURATIONS



NOMENCLATURE

Example Product Code

AK S 125 NR 2448 NF

NF = No Floats WF = With Floats

Size - Diameter X Height:

Simplex:	Duplex:
2448 - 24" x 48"	3648 - 36" X 48"
2460 - 24" X 60"	3660 - 36" X 60"
2472 - 24" X 72"	3672 - 36" X 72"
2484 - 24" X 84"	3684 - 36" X 84"

NR = No Rails GR = Guide Rails

Discharge Size:

125 = 1.25" 200 = 2.00"

S = Simplex D = Duplex

Basin

FOR THE RGS2012, AGS2012 AND 1GD GRINDER PUMPS

RGS2012

SUBMERSIBLE
GRINDER PUMP



1GD

SUBMERSIBLE GRINDER PUMP
DUAL SEAL WITH OPTIONAL
SEAL SENSOR PROBE




AGS

AXIAL GRINDER PUMP



TYPICAL INSTALLATION



INSTALLATION INSTRUCTIONS

- Basin Covers are solid. Vent must be field installed per local code.
- Basins are not pre-drilled for electrical grommet or inlet grommet. Parts are shipped loose. Grommet holes are field installed.

GUIDE RAIL EQUIPPED BASINS 1.25" DISCHARGE

Part Number	Description	Discharge Depth
AKS125GR2448NF	Simplex 24" X 48" No Floats	12"
AKS125GR2460NF	Simplex 24" x 60" No Floats	24"
AKS125GR2472NF	Simplex 24" X 72" No Floats	36"
AKS125GR2484NF	Simplex 24" X 84" No Floats	48"
AKS125GR2448WF	Simplex 24" X 48" With Floats	12"
AKS125GR2460WF	Simplex 24" X 60" With Floats	24"
AKS125GR2472WF	Simplex 24" X 72" With Floats	36"
AKS125GR2484WF	Simplex 24" X 84" With Floats	48"
AKD125GR3648NF	Duplex 36" X 48" No Floats	12"
AKD125GR3660NF	Duplex 36" X 60" No Floats	24"
AKD125GR3672NF	Duplex 36" X 72" No Floats	36"
AKD125GR3684NF	Duplex 36" X 84" No Floats	48"
AKD125GR3648WF	Duplex 36" X 48" With Floats	12"
AKD125GR3660WF	Duplex 36" X 60" With Floats	24"
AKD125GR3672WF	Duplex 36" X 72" With Floats	36"
AKD125GR3684WF	Duplex 36" X 84" With Floats	48"

GUIDE RAIL EQUIPPED BASINS 2.00" DISCHARGE

Part Number	Description	Discharge Depth
AKS200GR2448NF	Simplex 24" X 48" No Floats	12"
AKS200GR2460NF	Simplex 24" x 60" No Floats	24"
AKS200GR2472NF	Simplex 24" X 72" No Floats	36"
AKS200GR2484NF	Simplex 24" X 84" No Floats	48"
AKS200GR2448WF	Simplex 24" X 48" With Floats	12"
AKS200GR2460WF	Simplex 24" X 60" With Floats	24"
AKS200GR2472WF	Simplex 24" X 72" With Floats	36"
AKS200GR2484WF	Simplex 24" X 84" With Floats	48"
AKD200GR3648NF	Duplex 36" X 48" No Floats	12"
AKD200GR3660NF	Duplex 36" X 60" No Floats	24"
AKD200GR3672NF	Duplex 36" X 72" No Floats	36"
AKD200GR3684NF	Duplex 36" X 84" No Floats	48"
AKD200GR3648WF	Duplex 36" X 48" With Floats	12"
AKD200GR3660WF	Duplex 36" X 60" With Floats	24"
AKD200GR3672WF	Duplex 36" X 72" With Floats	36"
AKD200GR3684WF	Duplex 36" X 84" With Floats	48"

NON GUIDE RAIL EQUIPPED BASINS 1.25" DISCHARGE

Part Number	Description	Discharge Depth
AKS125NR2448NF	Simplex 24" X 48" No Floats	12"
AKS125NR2460NF	Simplex 24" x 60" No Floats	24"
AKS125NR2472NF	Simplex 24" X 72" No Floats	36"
AKS125NR2484NF	Simplex 24" X 84" No Floats	48"
AKS125NR2448WF	Simplex 24" X 48" With Floats	12"
AKS125NR2460WF	Simplex 24" X 60" With Floats	24"
AKS125NR2472WF	Simplex 24" X 72" With Floats	36"
AKS125NR2484WF	Simplex 24" X 84" With Floats	48"
AKD125NR3648NF	Duplex 36" X 48" No Floats	12"
AKD125NR3660NF	Duplex 36" X 60" No Floats	24"
AKD125NR3672NF	Duplex 36" X 72" No Floats	36"
AKD125NR3684NF	Duplex 36" X 84" No Floats	48"
AKD125NR3648WF	Duplex 36" X 48" With Floats	12"
AKD125NR3660WF	Duplex 36" X 60" With Floats	24"
AKD125NR3672WF	Duplex 36" X 72" With Floats	36"
AKD125NR3684WF	Duplex 36" X 84" With Floats	48"

NON GUIDE RAIL EQUIPPED BASINS 2.00" DISCHARGE

Part Number	Description	Discharge Depth
AKS200NR2448NF	Simplex 24" X 48" No Floats	12"
AKS200NR2460NF	Simplex 24" x 60" No Floats	24"
AKS200NR2472NF	Simplex 24" X 72" No Floats	36"
AKS200NR2484NF	Simplex 24" X 84" No Floats	48"
AKS200NR2448WF	Simplex 24" X 48" With Floats	12"
AKS200NR2460WF	Simplex 24" X 60" With Floats	24"
AKS200NR2472WF	Simplex 24" X 72" With Floats	36"
AKS200NR2484WF	Simplex 24" X 84" With Floats	48"
AKD200NR3648NF	Duplex 36" X 48" No Floats	12"
AKD200NR3660NF	Duplex 36" X 60" No Floats	24"
AKD200NR3672NF	Duplex 36" X 72" No Floats	36"
AKD200NR3684NF	Duplex 36" X 84" No Floats	48"
AKD200NR3648WF	Duplex 36" X 48" With Floats	12"
AKD200NR3660WF	Duplex 36" X 60" With Floats	24"
AKD200NR3672WF	Duplex 36" X 72" With Floats	36"
AKD200NR3684WF	Duplex 36" X 84" With Floats	48"



Xylem Inc.
 Phone: (866) 325-4210
 Fax: (888) 322-5877
www.xylem.com/goulds

Goulds is a registered trademark of Goulds Pumps, Inc. and is used under license.
 © 2020 Xylem Inc. BGRPKG R1 June 2020