

# 1088 Rotary Autosampler

## Autosampler for the Aurora 1030 TOC Analyzer



- Automates introduction of 88 samples to the Aurora 1030 TOC Analyzer
- Configurable for pre-acidification and sparging of sample TIC content within the autosampler to reduce TOC analysis time
- Performs programmable rinse steps via an integral wash station to clean the sampling needle and prevent cross-contamination
- Magnetic stirring ensures insoluble and particulated samples are homogeneous for accurate results
- Fits directly under the Aurora 1030 TOC analyzer to minimize laboratory benchspace requirements
- Supports sampling from open vials and septum piercing of sealed vials

### Description and Function

The 1088 Rotary Autosampler is specifically designed to operate with an Aurora 1030 TOC analyzer. The 1088 autosampler aspirates liquid samples from vials and transfers each sample aliquot to an Aurora 1030 TOC analyzer for analysis. A removable 88-position autosampler tray loads the sample vials for fully automated, unattended operation.

The 1088 supports a number of special functions to address a range of sample conditions and analysis requirements. Onboard magnetic stirring ensures samples containing insoluble components or particles are homogeneous for sampling and accurate analysis. Septum piercing provides closed vial sampling for applications where open vials may compromise the accuracy of measurements. System configuration for sample pretreatment allows pre-acidification and purging of samples within the 1088 prior to sampling. This technique removes the TIC content of samples, reducing the analysis time required for TOC measurements.

### Operating Principle

The sampling sequence of the 1088 autosampler is user-programmed through the Aurora 1030 touchscreen display. A stepper motor drive positions the appropriate vial below the sampling needle. The needle mechanism then lowers into the vial, aspirates the specified sample volume, and transfers it to the reaction chamber of Aurora 1030. Following sample transfer, the sampling needle returns to a wash station to be rinsed. A user-programmable number of rinses are then performed to clean the needle before the next vial is sampled.

### Principal Applications

- Drinking water
- Wastewater
- Ultrapure water
- Cleaning validation
- Water for injection
- Groundwater
- Surface water
- Industrial process water
- Seawater

### Sampling Methods

- Open vial
- Septum piercing

## Specifications

<b>Dimensions (1088 Autosampler)</b>	64.77–cm H x 38.1–cm W x 48.26–cm D (25.5” H x 15” W x 19” D)
<b>Weight (1088 Autosampler)</b>	19 kg (42 lbs)
<b>Dimensions (1088 Autosampler &amp; Aurora 1030)</b>	66–cm H x 47–cm W x 66–cm D (26” H x 18.5” W x 26” D)
<b>Weight (1088 Autosampler &amp; Aurora 1030)</b>	34.4 kg (76 lbs)
<b>Benchspace Footprint</b>	3,102 cm <sup>2</sup> (494 in <sup>2</sup> )
<b>Environment</b>	15–35 °C operating temperature 10–90% relative humidity
<b>Sample Capacity</b>	88 sample vials
<b>Sampling Needle</b>	8.4”, two-hole, stainless steel
<b>Sample Transfer Tubing</b>	0.045” I.D. x 1/8” O.D. Teflon <sup>®</sup> tubing
<b>Vials</b>	40-mL VOA vials
<b>Caps</b>	Open-hole caps
<b>Septa</b>	TFE-faced septa
<b>Sample Transfer Volume Range</b>	10 µL–10 mL
<b>Particulate Handling</b>	Up to 500 µm
<b>Special Functions</b>	On-board magnetic stirring Septum piercing Sample pre-treatment for TIC removal
<b>Power Supply</b>	100–230 V <sub>AC</sub> (±10%); 50/60 Hz; 150 W (max)
<b>Communication</b>	RS-485 (Aurora 1030 analyzer to 1088 Autosampler)
<b>Certifications</b>	CE
<b>Warranty</b>	12 months on parts and labor

### Autosampler Tray with Vials



### Programmable Autosampler Parameters

Config - Sample Intro - Rotary Autosampler

Sample Tray Type:  40mL X 88 vials

Sample Inlet Volume:

Sample Needle Depth (%):

Wash Needle Depth (%):

Sample Stirring Speed:

Wash Needle at Start of Sample  
Number of Needle Washes:

Wash Needle at End of Sequence  
Number of Needle Washes:

Vial Type:  
 Open  
 Closed

Microsoft and Windows are registered trademarks of Microsoft Corporation.  
Teflon is a registered trademark of E.I. DuPont de Nemours, Inc.

Publication 22700808