



Series 1510 Centrifugal Pump Kits

PUMP KITS INCLUDE:

1. Full Size Bronze Impeller
2. Cast Iron Volute
3. Volute Cover Plate and Gasket

4. Nameplate
5. Impeller Cap Screw and Washer

ACCESSORY KITS INCLUDE:

1. Support Foot
2. Motor Saddle (if required)
3. Pump Riser (if required)

BRONZE FITTED PUMPS

PUMP SIZE	MOTOR FRAME	PUMP KIT PART NO.	COUPLER PART NO.	BEARING ASSY. PART NO.	SEAL KIT PART NO.	BASE PART NO.	ACCESSORY KIT
1/4 AC	56	191310	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
1/2 AC	56	191602	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
2 AC	56	191312	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
	254T		186873			P85288	191979
2 1/2 AB	56	191314	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
	254T		186873			P85288	191979
3 AC	143 - 145T	191600	186869	185011	186862	P85285	191970
	182 - 184T		186870			P85286	191972
4 AC	143 - 145T	191552	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
	213T		186871			P85287	191976
5 A	182 - 184T	191554	186870	185011	186862	P85286	191993
	213 - 215T		186871			P85287	191978
1/4 BC	143 - 145T	191311	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
1/2 BC	143 - 145T	191470	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
	213 - 215T		186871			P85287	191976
2 BC	143 - 145T	191313	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
	213 - 215T		186871			P85287	191976
2 1/2 BB	182 - 184T	191315	186870	185011	186862	P85286	191973
	213 - 215T		186871			P85287	191976
3 BC	182 - 184T	191603	186870	185011	186862	P85286	191973
	213 - 215T		186871			P85287	191976
	254T		186873			P85288	191979
4 BC	213 - 215T	191316	186871	185011	186862	P85287	191978
	254T		186873			P85288	191981

DATA SHEET CP-521F (CONTINUED)

PUMP SIZE	MOTOR FRAME	PUMP KIT PART NO.	COUPLER PART NO.	BEARING ASSY. PART NO.	SEAL KIT PART NO.	BASE PART NO.	ACCESSORY KIT
5 BC	213 - 215T 254T	191576	186871 186873	185011	186862	P85289 P85289	191994 191995
5 BC	256T 284T	191568	186874 P63242	185014	186543	P85289 P85290	191990 191984
6 BC	254T 256T 284T	191584	P63239 186874 P63242	185014	186543	P85289 P85289 P85290	191990 191990 191984
2E	184T 213 - 215T 254T	191299	186870 186871 186873	185011	186862	P85298 P85298 P85298	191993 191978 191981
3E	213 - 215T 254T	191300	186871 186873	185011	186862	P85298	191978 191981
3E	256T	191301	186874	185014	186543	P85289	191989
4E	215T 254T	191302	186871 186873	185011	186862	P85298 P85298	191978 191981
4E	256T 284T	191303	186874 P63242	185014	186543	P85289 P85290	191989 191985
5E	254T 256T 284T 286T 324T	191304	P63239 186874 P63242 P63244 P63245	185014	186543	P85289 P85289 P85290 P85290 P85290	191990 191990 191984 191984 191996
6E	284T 286T 324T 326T 364T	191305	P63242 P63244 P63245 P63247 P63248	185014	186543	P85291 P85291 P85291 P85291 P85291	191986 191986 191987 191987 191988
2 G	213 - 215T 254T 256T	191325	186872 P63239 186874	185014	186543	P85289 P85289 P85289	191982 191989 191989
3 G	213 - 215T 254T 256T 284T	191326	186872 P63239 186874 P63242	185014	186543	P85289 P85289 P85289 P85290	191982 191989 191989 191985
4 GB	213 - 215T 254T 256T 284T 286T	191605	186872 P63239 186874 P63242 P63244	185014	186543	P85289 P85289 P85289 P85290 P85290	191983 191990 191990 191984 191984
5 G	254T 256T 284T 286T 324T 326T	191328	P63239 186874 P63243 P63244 P63245 P63247	185014	186543	P85291 P85291 P85291 P85291 P85291 P85291	191991 191991 191986 191986 191987 191987
6 G*	256T 284T 286T 324T 326T 364T 365T 404TS	191329	186874 P63243 P63244 P63245 P63247 P63248 P63250 P63253	185014	186543	P85291 P85291 P85291 P85291 P85291 P85291 P85291 P85291	191991 191986 191986 191987 191987 191988 191988 191992

* Large Bearing Frame Only, maximum impeller diameter 12 1/2".



Xylem Inc.
8200 N. Austin Avenue
Morton Grove, Illinois 60053
Phone: (847) 966-3700
Fax: (847) 965-8379
www.bellgossett.com