

3885 2EC

PUMP TO PANEL PART NUMBERS

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
2EC0311L	0.33	1	115	10.7	C4S10020	C4D10020
2EC0318L	0.33	1	208	6.8	C4S10020	C4D10020
2EC0312L	0.33	1	230	4.9	C4S10020	C4D10020
2EC0311	0.33	1	115	10.7	C4S10020	C4D10020
2EC0318	0.33	1	208	6.8	C4S10020	C4D10020
2EC0312	0.33	1	230	4.9	C4S10020	C4D10020
2EC0511	0.5	1	115	14.5	C4S10020	C4D10020
2EC0518	0.5	1	208	8.1	C4S10020	C4D10020
2EC0512	0.5	1	230	7.3	C4S10020	C4D10020
2EC0538	0.5	3	200	4.9	C4S34063	C4D34063
2EC0532	0.5	3	230	3.3	C4S32540	C4D32540
2EC0534	0.5	3	460	1.7	C4S31625	C4D31625
2EC0537	0.5	3	575	1.4	C4S31625	C4D31625
2EC0511H	0.5	1	115	14.5	C4S10020	C4D10020
2EC0518H	0.5	1	208	8.1	C4S10020	C4D10020
2EC0512H	0.5	1	230	7.3	C4S10020	C4D10020
2EC0538H	0.5	3	200	4.9	C4S34063	C4D34063
2EC0532H	0.5	3	230	3.6	C4S32540	C4D32540
2EC0534H	0.5	3	460	1.8	C4S31625	C4D31625
2EC0537H	0.5	3	575	1.5	C4S31625	C4D31625
2EC0718	0.75	1	208	11	C4S10020	C4D10020
2EC0712	0.75	1	230	10	C4S10020	C4D10020
2EC0738	0.75	3	200	6.2	C4S36310	C4D36310
2EC0732	0.75	3	230	5.4	C4S34063	C4D34063
2EC0734	0.75	3	460	2.7	C4S32540	C4D32540
2EC0737	0.75	3	575	2.2	C4S31625	C4D31625
2EC1018	1	1	208	14	C4S10020	C4D10020
2EC1012	1	1	230	12.5	C4S10020	C4D10020
2EC1038	1	3	200	8.1	C4S36310	C4D36310
2EC1032	1	3	230	7	C4S36310	C4D36310
2EC1034	1	3	460	3.5	C4S32540	C4D32540
2EC1037	1	3	575	2.8	C4S32540	C4D32540
2EC1518	1.5	1	208	17.5	C4S10020	C4D10020

Pump	HP	Phase	Voltage	Amps	Simplex Panel	Duplex Panel
2EC1512	1.5	1	230	15.7	C4S10020	C4D10020
2EC1538	1.5	3	200	10.6	C4S31016	C4D31016
2EC1532	1.5	3	230	9.2	C4S36310	C4D36310
2EC1534	1.5	3	460	4.6	C4S34063	C4D34063
2EC1537	1.5	3	575	3.7	C4S32540	C4D32540
2EC1518H	1.5	1	208	17.5	C4S10020	C4D10020
2EC1512H	1.5	1	230	15.7	C4S10020	C4D10020
2EC1538H	1.5	3	200	10.6	C4S31016	C4D31016
2EC1532H	1.5	3	230	9.2	C4S36310	C4D36310
2EC1534H	1.5	3	460	4.6	C4S34063	C4D34063
2EC1537H	1.5	3	575	3.7	C4S32540	C4D32540
2EC2012	2	1	230	18	C4S10020	C4D10020
2EC2038	2	3	200	12	C4S31016	C4D31016
2EC2032	2	3	230	11.6	C4S31016	C4D31016
2EC2034	2	3	460	5.8	C4S34063	C4D34063
2EC2037	2	3	575	4.7	C4S34063	C4D34063



Xylem Inc.
Phone: (847) 966-3700
Fax: (847) 965-8379
www.xylem.com/bellgossett

Xylem and Bell & Gossett are registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are property of their respective owners.

© 2024 Xylem Inc. BGC438852EC-PL123 R1 March 2024