



4DWC

PUMP-TO-PANEL PART NUMBERS

Order Number	HP	Volts	S.F. Amps	Simplex 3 Phase Panel Part Number	Duplex 3 Phase Panel Part Number
4DWC4K2A2M1C	7.5	200	27	NSS32432	NSD32432
4DWC4K3A2M1C		230	23.4	NSS32432	NSD32432
4DWC4K4A2M1C		460	11.7	NSS39014	NSD39014
4DWC4K5A2M1C		575	9.4	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4L2A2K1C	10	200	35.6	NSS33040	NSD33040
4DWC4L3A2K1C		230	31	NSS33040	NSD33040
4DWC4L4A2K1C		460	15.5	NSS31318	NSD31318
4DWC4L5A2K1C		575	12.3	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4M2A2G1C	15	200	54.8	NSS34865	NSD34865
4DWC4M3A2G1C		230	47.8	NSS34865	NSD34865
4DWC4M4A2G1C		460	23.9	NSS32432	NSD32432
4DWC4M5A2G1C		575	19.1	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4N2A2E1C	20	200	74.8	NSS365115	NSD365115
4DWC4N3A2E1C		230	65	NSS365115	NSD365115
4DWC4N4A2E1C		460	32.5	NSS33040	NSD33040
4DWC4N5A2E1C		575	26.0	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4P2A2C1C	25	200	83.6	NSS365115	NSD365115
4DWC4P3A2C1C		230	72.8	NSS365115	NSD365115
4DWC4P4A2C1C		460	36.4	NSS33040	NSD33040
4DWC4P5A2C1C		575	29.1	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4Q2A2B1C	30	200	103.2	NSS365115	NSD365115
4DWC4Q3A2B1C		230	89.6	NSS365115	NSD365115
4DWC4Q4A2B1C		460	44.8	NSS33750	NSD33750
4DWC4Q5A2B1C		575	35.8	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4R2A2A1C	40	200	132.8	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4R3A2A1C		230	115.4	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4R4A2A1C		460	57.7	NSS34865	NSD34865
4DWC4R5A2A1C		575	46.2	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4K2A3D1C	7.5	200	30.4	NSS33040	NSD33040
4DWC4K3A3D1C		230	26.4	NSS32432	NSD32432
4DWC4K4A3D1C		460	13.2	NSS31318	NSD31318
4DWC4K5A3D1C		575	10.6	Consult factory for custom quote.	Consult factory for custom quote.
4DWC4L2A3A1C	10	200	40	NSS3750	NSD33750
4DWC4L3A3A1C		230	34.8	NSS33040	NSD33040
4DWC4L4A3A1C		460	17.4	NSS31723	NSD31723
4DWC4L5A3A1C		575	13.9	Consult factory for custom quote.	Consult factory for custom quote.



Xylem Inc.
 2881 East Bayard Street Ext., Suite A
 Seneca Falls, NY 13148
 Phone: (866) 325-4210 • Fax: (888) 322-5877
www.xylem.com/bellgossett

Xylem and Bell & Gossett are registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are property of their respective owners.