

# Winlog.x Family

Last change: 13.06.2018

Software/Features	Winlog.basic	Winlog.light	Winlog.pro	Winlog.med	Winlog.validation	Winlog.wave	Winlog.web
Current Release	V2.8	V2.8	V2.8	V3.71	V3.71	V2.27	V3.5
Event Triggered Recording			●	●	●		●
Script-Calculations			●				●
System-Scripts			●				
Picture Manager			●		●		
Measure in Charts			●				
Cursor		●	●	●	●		
Realtime Calculations			●	●	●		●
Ranges			●	●	●		
Range-based Calculations			●	●	●		
Statistics per Range			●	●	●		
Relative Time Axis			●				
Configurations		●	●	●(2)	●(2)		
Firmware-Update		●	●	●	●		●
Import		●(1)	●(1)				
Calibration			●	●	●		
Automatic File Name Generation			●				
21 CFR Part 11	●	●	●	●	●	●	●
User Administration	●	●	●	●	●	●	●
Audit-Trail	●	●	●	●	●	●	●
Advanced Chart Features		●	●	●	●		
Multi Document Support		●	●	●	●		
Export (Excel, PDF)	●	●	●	●	●	●	●
Customizable Company Logo	●	●	●	●	●	●	●
Wireless Support			●	●	●	●	●
2D Placement		●	●		●	●	●
3D Placement					●		
Routine Check			●(3)	●	●		
Validation			●(3)		●		
Unit Administration	●	●	●	●	●	●	●
Split Measurements			●	●	●		
Advanced Alarm-Management (Zones)	●(5)	●(5)	●(5)				
Supported Logger Types	Winlog.basic	Winlog.light	Winlog.pro	Winlog.med	Winlog.validation	Winlog.wave	Winlog.web
EBI 1/2		●	●	●	●		●
EBI 6	●	●	●				
EBI 20	●	●	●	●(7)	●(7)		
EBI 30		●	●	●	●		
EBI 40		●	●	●(7)	●(7)		
EBI 10		●	●	●	●		
EBI 11		●	●	●	●		
EBI 12		●		●(13)	●(13)		
EBI 15				●	●		
EBI 25						●	●
EBI 100		●	●	●	●		
EBI 300	●(4)	●(4)	●(4)	●(7)	●(7)		
EBI 310	●(6)	●(6)	●(6)	●(7)	●(7)		
EBI 330	●(8)	●(8)	●(8)				
EBI 16				●(9)	●(9)		
PHT 830			●(11)	●(12)	●(12)		
CT 830			●(11)	●(12)	●(12)		
System Requirements	Winlog.basic	Winlog.light	Winlog.pro	Winlog.med	Winlog.validation	Winlog.wave	Winlog.web
Windows Vista 32 bit	●	●	●	●	●	●	●
Windows Vista 64 bit	●	●	●	●	●	●	●
Windows 7 / 32 bit	●	●	●	●	●	●	●
Windows 7 / 64 bit	●	●	●	●	●	●	●
Windows 8 / 32 bit	●	●	●	●	●	●	●
Windows 8 / 64 bit	●	●	●	●	●	●	●
Windows 10 / 32 bit	●	●	●	●	●	●	●
Windows 10 / 64 bit	●	●	●	●	●	●	●
Memory	>= 1GB	>= 1GB	>= 1GB	>= 1GB	>= 1GB	>= 1GB	>= 4 GB
Hard Disc Memory	> 300 MB	> 300 MB	> 300 MB	> 1 GB	> 1 GB	> 1 GB	> 20 GB
CD/DVD Drive	●	●	●	●	●	●	●
Screen Resolution <sup>(10)</sup>	>= 1024x768	>= 1024x768	>= 1024x768	>= 1024x768	>= 1024x768	>= 1024x768	>= 1024x768
Processor	Pentium 1GHz+	Pentium 1GHz+	Pentium 1GHz+	Pentium 1GHz+	Pentium 1GHz+	Pentium 1GHz+	Pentium 2GHz+
Market Overview	Winlog.basic	Winlog.light	Winlog.pro	Winlog.med	Winlog.validation	Winlog.wave	Winlog.web
Food	●	●	●			●	●
Industry	●	●	●		●	●	●
Pharmaceutical		●	●		●		●
Medical		●	●	●	●		
Available Languages	Winlog.basic	Winlog.light	Winlog.pro	Winlog.med	Winlog.validation	Winlog.wave	Winlog.web
English	●	●	●	●	●	●	●
French	●	●	●	●	●	●	●
Italian	●	●	●	●	●	●	●
Spanish	●	●	●	●	●	●	●
Chinese	●	●	●	●	●	●	●
Japanese	●	●	●	●	●	●	●
Korean			●	●	●		
Portuguese				●	●		
Greek				●	●		
Czech	●	●	●	●	●		
Swedish	●	●	●	●	●		
Dutch	●	●	●	●	●		
German	●	●	●	●	●	●	●
Turkish				●	●		
Polish				●	●		
Norwegian				●	●		
Slovak				●	●		

(1) Winlog.basic, Winlog.2000, Winlog.Validation  
 (2) Template based  
 (3) Manual

(4) Since V2.5  
 (5) Only EBI310  
 (6) Since V2.6  
 (7) Since V3.3  
 (8) Since V2.63  
 (9) Since V3.5

(10) On standard view (100 %)  
 (11) Since V2.7  
 (12) Since V3.62

(13) Since V3.70