







































Beverage Pump Liquid & Gas Fittings

LIQUID OR GAS	PART CATEGORY	PART NUMBER	DESCRIPTION	PUMP COMPATIBILITY	MATERIAL	PICTURE
Liquid Fittings	Stainless Steel Hose Barbs	20324030	¼" (6.3 mm) Hose Barb, Straight	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Stainless Steel	
Liquid Fittings	Stainless Steel Hose Barbs	20325030	¾" (9.5 mm) Hose Barb, Straight	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Stainless Steel	
Liquid Fittings	Stainless Steel Hose Barbs	20606100	½" (12.7 mm) Hose Barb, Straight	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Stainless Steel	
Liquid Fittings	Stainless Steel Hose Barbs	20607100	¼" (6.3 mm) Hose Barb, Elbow	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Stainless Steel	
Liquid Fittings	Stainless Steel Hose Barbs	20608100	¾" (9.5 mm) Hose Barb, Elbow	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Stainless Steel	
Liquid Fittings	Stainless Steel Hose Barbs	20450000	3/8" (9.5 mm) Hose Barb Straight	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Stainless Steel	
Liquid Fittings	Plastic Product Outlets & Inlets	20325031	¾" (9.5 mm) Hose Barb, Straight	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Plastic	
Liquid Fittings	Plastic Product Outlets & Inlets	20381026	10-13mm (¾"-½") Hose Barb, Straight	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	Plastic Product Outlets & Inlets	20455132	¾" (9.5 mm) Hose Barb, Straight 2 O-rings Quad Port	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	Plastic Product Outlets & Inlets	20381002	½" (12.7 mm) Hose Barb, Straight	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	Plastic Product Outlets & Inlets	20381024	10-13mm (¾"-½") Hose Barb, Elbow	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	Plastic Product Outlets & Inlets	20381009	½" (12.7 mm) Hose Barb, Elbow	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	Plastic Product Outlets & Inlets	21000912	3/8" (9.5mm) Hose Barb Elbow	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Plastic	
Liquid Fittings	Plastic Product Outlets & Inlets	20793201	1/4" (6.3mm) Hose Barb	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Plastic	

Beverage Pump Liquid & Gas Fittings

LIQUID OR GAS	PART CATEGORY	PART NUMBER	DESCRIPTION	PUMP COMPATIBILITY	MATERIAL	PICTURE
Liquid Fittings	John Guest Style - Quick Fit	21000231B	¼" (6.3 mm) O.D. Tubing	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Plastic	
Liquid Fittings	John Guest Style - Quick Fit	21000232B	¾" (9.5 mm) O.D. Tubing	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Plastic	
Liquid Fittings	John Guest Style - Quick Fit	21000679A	5/16" (7.9mm) OD Tubing Elbow Fittings	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Plastic	
Liquid Fittings	John Guest Style - Quick Fit	21000685A	3/16" (4.8mm) OF Tubing Elbow Fittings	G55, G5A, G80, T5000 Series, M Series, LFP Series, BLC Series	Plastic	
Liquid Fittings	John Guest Style - Quick Fit	21000228B	For use with ¼" (6.3 mm) O.D. Tubing	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	John Guest Style - Quick Fit	21000229B	For use with ¾" (9.5 mm) O.D. Tubing	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	John Guest Style - Quick Fit	21000230B	For use with ½" (12.7 mm) O.D. Tubing	G56, K56, G81, G60 Series, 01752 & 01754 Series Water Pressure Regulators	Plastic	
Liquid Fittings	Threaded Barb Fittings	91010001	¾" NPT Male x ¾" (9.5 mm) Barb Elbow	DupleX Duplex II HP Triplex	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010002	¾" NPT Male x ¾" (9.5 mm) Barb Straight	DupleX Duplex II HP Triplex	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010003	¼" NPT Male x ¾" (9.5 mm) Barb Elbow	2125 Series	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010004	¼" NPT Male x ¾" (9.5 mm) Barb Straight	2125 Series	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010005	¾" NPT Male x ½" (12.7 mm) Barb Elbow	DupleX Duplex II HP Triplex	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010006	¾" NPT Male x ½" (12.7 mm) Barb Straight	DupleX Duplex II HP Triplex	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010032	¾" NPT Male x ¼" (6.3 mm) Barb Straight	DupleX Duplex II HP Triplex	Nylon	

Beverage Pump Liquid & Gas Fittings

LIQUID OR GAS	PART CATEGORY	PART NUMBER	DESCRIPTION	PUMP COMPATIBILITY	MATERIAL	PICTURE
Liquid Fittings	Threaded Barb Fittings	91010033	3/8" NPT Male x 1/4" (6.3 mm) Barb Elbow	Duplex Duplex II HP Triplex	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010052	1/4" NPT Male x 1/4" (6.3 mm) Barb Elbow	2125 Series	Nylon	
Liquid Fittings	Threaded Barb Fittings	91010053	1/4" NPT Male x 1/4" (6.3 mm) Barb Straight	2125 Series	Nylon	
Gas Fittings	Gas Pump Air Inlet Fittings	01510000	1/4" (6.3 mm) Hose Barb, Straight	G5X, G60, G80, T5000 Series, M Series	Brass	
Gas Fittings	Gas Pump Air Inlet Fittings	01520000	1/4" (6.3 mm) Hose Barb, Tee	G5X, G60, G80, T5000 Series, M Series	Brass	
Gas Fittings	Gas Pump Air Inlet Fittings	01521000	1/4" (6.3 mm) Hose Barb, Elbow	G5X, G60, G80, T5000 Series, M Series	Brass	
Gas Fittings	Offset Gas Inlet Fittings	01522000	1/4" Offset CO2 Tee fitting	G5X, G60, G80, T5000 Series, M Series	Brass	
Gas Fittings	Offset Gas Inlet Fittings	01523000	1/4" Offset CO2 Left Hand	G5X, G60, G80, T5000 Series, M Series	Brass	
Gas Fittings	Offset Gas Inlet Fittings	01524000	1/4" Offset CO2 Right Hand	G5X, G60, G80, T5000 Series, M Series	Brass	
Gas Fittings	John Guest Style Quick Fit Gas Inlet fitting	21000234B	Brass CO2 Fitting with shutoff, for use with 1/4" (6.3 mm) O.D. tubing	G5X, G60, G80, T5000 Series, M Series	Brass	
Gas Fittings	John Guest Style Quick Fit Gas Inlet fitting	1510101	Plastic CO2 inlet Fitting with shutoff, for use with 3/8" (9.5 mm) O.D. tubing	G5X, G60, G80, T5000 Series, M Series	Plastic	