

OCT 15

Supersedes all previous issues

PUMP	SIZE	3x2x6.5F-L	4x3x9F
	TYPE	2000	2000
STAGES		1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	125
	DISCHARGE	125	125
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	CAST IRON ASTM A48 CLASS 35
MAX DISCHARGE PRESSURE (PSIG)		200	200
MAX SUCTION PRESSURE (PSIG)		100	100
MAX HYDROSTATIC PRESSURE (PSIG)		375	375
CASING WALL THICKNESS		0.31	0.38

STUFFING BOX DESIGN

BORE	2.00	2.62
DEPTH	2.00	2.02
PACKING: # RINGS / SIZE SQUARE	5 / .38	5 / .44
SEAL CAGE WIDTH	0.38	0.38
SHAFT SLEEVE O.D.	1.25	1.62

IMPELLER DESIGN

# OF VANES	6	6
INLET AREA (IN ²)	7.30	12.80
MAX DIAMETER	6.50	9.00
MIN DIAMETER	4.00	6.50
MAX SPHERE	0.50	0.81
WR ² FOR MAX DIA (LBS-FT ²)	0.40	0.80
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		0.875	1.250
DIA THRU SLEEVE		1.000	1.375
DIA AT COUPLING		0.875	1.375
SHAFT SPAN - BRG TO BRG		3.74	7.62
BALL BEARING	INBOARD BRG #	6306	6308
	DIA THRU BRG	1.1816	1.5753
	OUTBOARD BRG #	6306	6308
	DIA THRU BRG	1.1816	1.5753
FRAME NUMBER		330	500
INSTRUCTION BOOK		AC8652	AC8652

"H" PREFIX INDICATES HIGH PRESSURE CASING

Supersedes all previous issues

PUMP	SIZE	3x2x11F-S	H3x2x11F-S	6x4x9F	H6x4x9F	6x4x10F-M	H6x4x10F-M
	TYPE	8100	8100	8100	8100	8100	8100
STAGES		1	1	1	1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	250	125	125 OR 250	125	125 OR 250
	DISCHARGE	125	250	125	250	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		200	400	200	375	200	450
MAX SUCTION PRESSURE (PSIG)		75	300	100	200	100	200
MAX HYDROSTATIC PRESSURE (PSIG)		262	600	375	563	375	675
CASING WALL THICKNESS		0.38	0.38	0.44	0.44	0.5	0.5

STUFFING BOX DESIGN

BORE	2.62	2.62	2.62	2.62	3.25	3.25
DEPTH	2.56	2.56	2.56	2.56	3.50	3.50
PACKING: # RINGS / SIZE SQUARE	5 / .38	5 / .38	5 / .38	5 / .38	5 / .50	5 / .50
SEAL CAGE WIDTH	0.50	0.50	0.50	0.50	0.75	0.75
SHAFT SLEEVE O.D.	1.88	1.88	1.88	1.88	2.25	2.25

IMPELLER DESIGN

# OF VANES	6	6	6	6	6	6
INLET AREA (IN ²)	7.70	7.70	5.90	5.90	15.90	15.90
MAX DIAMETER	11.00	11.00	9.80	9.80	12.00	12.00
MIN DIAMETER	5.50	5.50	6.00	6.00	6.50	6.50
MAX SPHERE	0.25	0.25	0.44	0.44	0.50	0.50
WR ² FOR MAX DIA (LBS-FT ²)	3.60	3.60	2.40	2.40	2.90	2.90
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		1.686	1.686	1.687	1.687	1.937	1.937
DIA THRU SLEEVE		1.499	1.499	1.499	1.499	1.874	1.874
DIA AT COUPLING		1.125	1.125	1.125	1.125	1.375	1.375
SHAFT SPAN - BRG TO BRG		20.90	20.90	22.00	22.00	25.25	25.25
BALL BEARING	INBOARD BRG #	6206	6206	6206	6206	6208	6208
	DIA THRU BRG	1.1816	1.1816	1.1816	1.1816	1.5753	1.5753
	OUTBOARD BRG #	5206	5206	5206	5206	5307	5307
	DIA THRU BRG	1.1160	1.1160	1.1816	1.1816	1.3785	1.3785
FRAME NUMBER		F20-A4	F20-A5	F20-G4	F20-G4	F20-B4	F20-B4
INSTRUCTION BOOK		AC6102	AC6102	AC6102	AC6102	AC6102	AC6102

OCT 15

Supersedes all previous issues

"H" PREFIX INDICATES HIGH PRESSURE CASING

PUMP	SIZE	6x4x11F	H6x4x11F	6x4x12F-M	H6x4x12F-M	6x6x9F	H6x6x9F
	TYPE	8100	8100	8100	8100	8100	8100
STAGES		1	1	1	1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	125 OR 250	125	125 OR 250	125	250
	DISCHARGE	125	250	125	250	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		200	400	200	375	200	375
MAX SUCTION PRESSURE (PSIG)		100	200	100	200	100	200
MAX HYDROSTATIC PRESSURE (PSIG)		375	600	338	563	375	563
CASING WALL THICKNESS		0.5	0.5	0.44	0.44	0.44	0.44

STUFFING BOX DESIGN

BORE	3.25	3.25	2.62	2.62	2.62	2.62
DEPTH	3.50	3.50	2.56	2.56	2.56	2.56
PACKING: # RINGS / SIZE SQUARE	5 / .50	5 / .50	5 / .38	5 / .38	5 / .38	5 / .38
SEAL CAGE WIDTH	0.75	0.75	0.50	0.50	0.50	0.50
SHAFT SLEEVE O.D.	2.25	2.25	1.88	1.88	1.88	1.88

IMPELLER DESIGN

# OF VANES	6	6	6	6	6	6
INLET AREA (IN ²)	19.60	19.60	10.20	10.20	5.90	5.90
MAX DIAMETER	11.60	11.60	13.70	13.70	9.80	9.80
MIN DIAMETER	6.50	6.50	7.50	7.50	6.50	6.50
MAX SPHERE	0.70	0.70	0.50	0.50	0.48	0.48
WR ² FOR MAX DIA (LBS-FT ²)	3.00	3.00	3.00	3.00	2.50	2.50
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		1.937	1.937	1.687	1.687	1.687	1.687
DIA THRU SLEEVE		1.874	1.874	1.499	1.499	1.499	1.499
DIA AT COUPLING		1.375	1.375	1.125	1.125	1.125	1.125
SHAFT SPAN - BRG TO BRG		25.25	25.25	22.90	22.90	22.00	22.00
BALL BEARING	INBOARD BRG #	6208	6208	6206	6206	6206	6206
	DIA THRU BRG	1.5753	1.5753	1.1816	1.1816	1.1816	1.1816
	OUTBOARD BRG #	5307	5307	5206	5206	5206	5206
	DIA THRU BRG	1.3785	1.3785	1.8160	1.8160	1.8160	1.8160
FRAME NUMBER		F20-B4	F20-B4	F20-C4	F20-C4	F20-G4	F20-G4
INSTRUCTION BOOK		AC6102	AC6102	AC6102	AC6102	AC6102	AC6102

"H" PREFIX INDICATES HIGH PRESSURE CASING

Supersedes all previous issues

PUMP	SIZE	8x6x9F	H8x6x9F	8x6x10F	H8x6x10F	8x6x12F-S	H8x6x12F-S
	TYPE	8100	8100	8100	8100	8100	8100
STAGES		1	1	1	1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	250	125	250	125	125 OR 250
	DISCHARGE	125	250	125	250	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		200	375	200	375	200	375
MAX SUCTION PRESSURE (PSIG)		100	200	100	200	100	200
MAX HYDROSTATIC PRESSURE (PSIG)		375	563	375	563	338	563
CASING WALL THICKNESS		0.44	0.44	0.44	0.44	0.44	0.44

STUFFING BOX DESIGN

BORE	2.62	2.62	3.25	3.25	2.62	2.62
DEPTH	2.56	2.56	3.50	3.50	2.56	2.56
PACKING: # RINGS / SIZE SQUARE	5 / .38	5 / .38	5 / .50	5 / .50	5 / .38	5 / .38
SEAL CAGE WIDTH	0.50	0.50	0.75	0.75	0.50	0.50
SHAFT SLEEVE O.D.	1.88	1.88	2.25	2.25	1.88	1.88

IMPELLER DESIGN

# OF VANES	6	6	6	6	5	5
INLET AREA (IN ²)	12.00	12.00	15.20	15.20	27.00	27.00
MAX DIAMETER	9.80	9.80	10.00	10.00	12.80	12.80
MIN DIAMETER	6.50	6.50	7.60	7.60	7.00	7.00
MAX SPHERE	0.64	0.64	0.75	0.75	0.72	0.72
WR ² FOR MAX DIA (LBS-FT ²)	2.60	2.60	3.10	3.10	3.60	3.60
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		1.687	1.687	1.937	1.937	1.687	1.687
DIA THRU SLEEVE		1.499	1.499	1.874	1.874	1.499	1.499
DIA AT COUPLING		1.125	1.125	1.375	1.375	1.125	1.125
SHAFT SPAN - BRG TO BRG		25.25	25.25	25.25	25.25	22.90	22.90
BALL BEARING	INBOARD BRG #	6206	6206	6208	6208	6206	6206
	DIA THRU BRG	1.1816	1.1816	1.5753	1.5753	1.1816	1.1816
	OUTBOARD BRG #	5206	5206	5307	5307	5206	5206
	DIA THRU BRG	1.1816	1.1816	1.3750	1.3750	1.1816	1.1816
FRAME NUMBER		F20-H4	F20-H4	F20-I4	F20-I4	F20-C4	F20-C4
INSTRUCTION BOOK		AC6102	AC6102	AC6102	AC6102	AC6102	AC6102

OCT 15

Supersedes all previous issues

"H" PREFIX INDICATES HIGH PRESSURE CASING

PUMP	SIZE	8x6x12F-M	H8x6x12F-M	8x6x13F	H8x6x13F	8x6x18F	H8x6x18F
	TYPE	8100	8100	8100	8100	8100	8100
STAGES		1	1	1	1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	250	125	250	125	250
	DISCHARGE	125	250	125	250	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		200	375	200	375	200	375
MAX SUCTION PRESSURE (PSIG)		100	200	75	200	100	200
MAX HYDROSTATIC PRESSURE (PSIG)		375	563	315	563	390	563
CASING WALL THICKNESS		0.5	0.44	0.44	0.44	0.44	0.44

STUFFING BOX DESIGN

BORE	3.25	3.25	3.25	3.25	3.25	3.25
DEPTH	3.50	3.50	3.50	3.50	3.50	3.50
PACKING: # RINGS / SIZE SQUARE	5 / .50	5 / .50	5 / .50	5 / .50	5 / .50	5 / .50
SEAL CAGE WIDTH	0.75	0.75	0.75	0.75	0.75	0.75
SHAFT SLEEVE O.D.	2.25	2.25	2.25	2.25	2.25	2.25

IMPELLER DESIGN

# OF VANES	5	5	7	7	6	6
INLET AREA (IN ²)	19.60	19.60	44.40	44.40	18.30	18.30
MAX DIAMETER	11.60	11.60	13.10	13.10	17.20	17.20
MIN DIAMETER	6.50	6.50	7.00	7.00	13.00	13.00
MAX SPHERE	0.70	0.70	1.00	1.00	0.70	0.70
WR ² FOR MAX DIA (LBS-FT ²)	3.00	3.00	5.30	5.30	18.00	18.00
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		1.937	1.937	1.937	1.937	1.937
DIA THRU SLEEVE		1.874	1.874	1.874	1.874	1.874
DIA AT COUPLING		1.375	1.375	1.375	1.375	1.375
SHAFT SPAN - BRG TO BRG		25.25	25.25	27.25	27.25	27.25
BALL BEARING	INBOARD BRG #	6208	6208	6208	6208	6208
	DIA THRU BRG	1.5753	1.5753	1.5753	1.5753	1.5753
	OUTBOARD BRG #	5307	5307	5307	5307	5307
	DIA THRU BRG	1.3785	1.3785	1.3785	1.3785	1.3785
FRAME NUMBER		F20-B4	F20-B4	F20-D4	F20-D4	F20-D4
INSTRUCTION BOOK		AC6102	AC6102	AC6102	AC6102	AC6102

"H" PREFIX INDICATES HIGH PRESSURE CASING

Supersedes all previous issues

PUMP	SIZE	8x8x12F	H8x8x12F	8x8x17F	H8x8x17F	10x8x17F-S	① H10x8x17F-S
	TYPE	8100	8100	8100	8100	8100	8100
STAGES		1	1	1	1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	125 OR 250	125	250	125	250
	DISCHARGE	125	250	125	250	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		200	400	200	375	200	375
MAX SUCTION PRESSURE (PSIG)		75	200	100	200	100	200
MAX HYDROSTATIC PRESSURE (PSIG)		300	600	338	563	300	555
CASING WALL THICKNESS		0.44	0.44	0.44	0.44	0.5	0.5

STUFFING BOX DESIGN

BORE	3.25	3.25	3.75	3.75	3.75	3.75
DEPTH	3.50	3.50	3.62	3.62	3.62	3.62
PACKING: # RINGS / SIZE SQUARE	5 / .50	5 / .50	5 / .50	5 / .50	5 / .50	5 / .50
SEAL CAGE WIDTH	0.75	0.75	0.94	0.94	0.94	0.94
SHAFT SLEEVE O.D.	2.25	2.25	2.75	2.75	2.75	2.75

IMPELLER DESIGN

# OF VANES	7	7	7	7	7	7
INLET AREA (IN ²)	61.90	61.90	40.20	40.20	57.50	57.50
MAX DIAMETER	12.80	12.80	17.70	17.70	17.00	17.00
MIN DIAMETER	8.00	8.00	10.00	10.00	10.00	10.00
MAX SPHERE	1.13	1.13	0.98	0.98	0.97	0.97
WR ² FOR MAX DIA (LBS-FT ²)	8.10	8.10	17.00	17.00	20.70	20.70
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		1.937	1.937	2.437	2.437	2.437	2.437
DIA THRU SLEEVE		1.874	1.874	2.374	2.374	2.374	2.374
DIA AT COUPLING		1.375	1.375	1.625	1.625	1.625	1.625
SHAFT SPAN - BRG TO BRG		27.25	27.25	29.90	29.90	29.90	29.90
BALL BEARING	INBOARD BRG #	6208	6208	6309	6309	6309	6309
	DIA THRU BRG	1.5753	1.5753	1.7500	1.7500	1.7500	1.7500
	OUTBOARD BRG #	5307	5307	5308	5308	5308	5308
	DIA THRU BRG	1.3785	1.3785	1.5753	1.5753	1.5753	1.5753
FRAME NUMBER		F20-D4	F20-D4	F20-E4	F20-E4	F20-E4	F20-E4
INSTRUCTION BOOK		AC6102	AC6102	AC6102	AC6102	AC6102	AC6102

① FM APPROVED ONLY

OCT 15

Supersedes all previous issues

"H" PREFIX INDICATES HIGH PRESSURE CASING

PUMP	SIZE	10x8x17F-L	① H10x8x17F-L	10x8x20F-S	H10x8x20F-S	10x8x20F-L	H10x8x20F-L
	TYPE	8100	8100	8100	8100	8100	8100
STAGES		1	1	1	1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	250	125	250	125	250
	DISCHARGE	125	250	125	250	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		200	375	200	375	200	375
MAX SUCTION PRESSURE (PSIG)		100	200	100	200	100	200
MAX HYDROSTATIC PRESSURE (PSIG)		300	555	300	555	262	555
CASING WALL THICKNESS		0.5	0.5	0.62	0.62	0.62	0.62

STUFFING BOX DESIGN

BORE	3.75	3.75	3.75	3.75	3.75	3.75
DEPTH	3.62	3.62	3.62	3.62	3.62	3.62
PACKING: # RINGS / SIZE SQUARE	5 / .50	5 / .50	5 / .50	5 / .50	5 / .50	5 / .50
SEAL CAGE WIDTH	0.94	0.94	0.94	0.94	0.94	0.94
SHAFT SLEEVE O.D.	2.75	2.75	2.75	2.75	2.75	2.75

IMPELLER DESIGN

# OF VANES	5	5	6	6	6	6
INLET AREA (IN ²)	65.60	65.60	68.40	68.40	74.00	74.00
MAX DIAMETER	17.30	17.30	20.70	20.70	20.20	20.20
MIN DIAMETER	12.00	12.00	12.00	12.00	12.00	12.00
MAX SPHERE	1.15	1.15	0.53	0.53	0.75	0.75
WR ² FOR MAX DIA (LBS-FT ²)	22.40	22.40	21.70	21.70	22.50	22.50
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		2.437	2.437	2.437	2.437	2.437
DIA THRU SLEEVE		2.374	2.374	2.374	2.374	2.374
DIA AT COUPLING		1.625	1.625	1.625	1.625	1.625
SHAFT SPAN - BRG TO BRG		29.90	29.90	29.90	29.90	29.90
BALL BEARING	INBOARD BRG #	6309	6309	6309	6309	6309
	DIA THRU BRG	1.7500	1.7500	1.7500	1.7500	1.7500
	OUTBOARD BRG #	5308	5308	5308	5308	5308
	DIA THRU BRG	1.5753	1.5753	1.5753	1.5753	1.5753
FRAME NUMBER		F20-E4	F20-E4	F20-E4	F20-E4	F20-E4
INSTRUCTION BOOK		AC6102	AC6102	AC6102	AC6102	AC6102

① FM APPROVED ONLY

"H" PREFIX INDICATES HIGH PRESSURE CASING

PUMP	SIZE	12x10x18F	H12x10x18F
	TYPE	8100	8100
STAGES		1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	250
	DISCHARGE	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		200	375
MAX SUCTION PRESSURE (PSIG)		100	200
MAX HYDROSTATIC PRESSURE (PSIG)		345	563
CASING WALL THICKNESS		0.56	0.56

STUFFING BOX DESIGN

BORE	3.75	3.75
DEPTH	3.62	3.62
PACKING: # RINGS / SIZE SQUARE	5 / .50	5 / .50
SEAL CAGE WIDTH	0.94	0.94
SHAFT SLEEVE O.D.	2.75	2.75

IMPELLER DESIGN

# OF VANES	8	8
INLET AREA (IN ²)	53.40	53.40
MAX DIAMETER	18.00	18.00
MIN DIAMETER	12.50	12.50
MAX SPHERE	0.90	0.90
WR ² FOR MAX DIA (LBS-FT ²)	24.20	24.20
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		2.437	2.437
DIA THRU SLEEVE		2.374	2.374
DIA AT COUPLING		1.625	1.625
SHAFT SPAN - BRG TO BRG		29.90	29.90
BALL BEARING	INBOARD BRG #	6309	6309
	DIA THRU BRG	1.7500	1.7500
	OUTBOARD BRG #	5308	5308
	DIA THRU BRG	1.5753	1.5753
FRAME NUMBER		F20-E4	F20-E4
INSTRUCTION BOOK		AC6102	AC6102

OCT 15

Supersedes all previous issues

"H" PREFIX INDICATES HIGH PRESSURE CASING

PUMP	SIZE	16X10X22F	H16X10X22F
	TYPE	8150	8150
STAGES		1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	125 OR 250
	DISCHARGE	125	250
CASING MATERIAL		DUCTILE IRON ASTM A536 GR 65-45-12	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		250	325
MAX SUCTION PRESSURE (PSIG)		100	200
MAX HYDROSTATIC PRESSURE (PSIG)		375	488
CASING WALL THICKNESS		0.72	0.72

STUFFING BOX DESIGN

BORE	5.25	5.25
DEPTH	4.0	4.0
PACKING: # RINGS / SIZE SQUARE	5 / .62	5 / .62
SEAL CAGE WIDTH	0.62	0.62
SHAFT SLEEVE O.D.	4.0	4.0

IMPELLER DESIGN

# OF VANES	4	4
INLET AREA (IN ²)	78.5	78.5
MAX DIAMETER	22.25	22.25
MIN DIAMETER	16.17	16.17
MAX SPHERE	1.05	1.05
WR ² FOR MAX DIA (LBS-FT ²)	74	74
WEAR RING CLEARANCE - DIAMETRICAL	.019-.023	.019-.023

SHAFT AND BEARING DATA

DIA THRU IMPELLER		3.625	3.625
DIA THRU SLEEVE		3.50	3.50
DIA AT COUPLING		3.125	3.125
SHAFT SPAN - BRG TO BRG		44.67	44.67
BALL BEARING	INBOARD BRG #	6316	6316
	DIA THRU BRG	3.150	3.150
	OUTBOARD BRG #	6316	6316
	DIA THRU BRG	3.150	3.150
FRAME NUMBER		-	-
INSTRUCTION BOOK		AC6102	AC6102

OCT 15

Supersedes all previous issues

"H" PREFIX INDICATES HIGH PRESSURE CASING

PUMP	SIZE	12x8x21F	H12x8x21F	12x8x22F-M	H12x8x22F-M	14x10x20F-S	H14x10x20F-S
	TYPE	9100	9100	9100	9100	9100	9100
STAGES		1	1	1	1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	250	125	250	125	250
	DISCHARGE	250	250	250	250	125	250
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12
MAX DISCHARGE PRESSURE (PSIG)		250	375	250	375	175	255
MAX SUCTION PRESSURE (PSIG)		100	200	100	200	100	200
MAX HYDROSTATIC PRESSURE (PSIG)		375	563	405	563	262	383
CASING WALL THICKNESS		0.62	0.62	0.62	0.62	0.62	0.62

STUFFING BOX DESIGN

BORE	5.12	5.12	5.12	5.12	5.12	5.12
DEPTH	4.81	4.81	4.81	4.81	4.81	4.81
PACKING: # RINGS / SIZE SQUARE	6 / .62	6 / .62	6 / .62	6 / .62	6 / .62	6 / .62
SEAL CAGE WIDTH	0.75	0.75	0.75	0.75	0.75	0.75
SHAFT SLEEVE O.D.	3.88	3.88	3.88	3.88	3.88	3.88

IMPELLER DESIGN

# OF VANES	6	6	5	5	6	6
INLET AREA (IN ²)	35.70	35.70	68.00	68.00	112.00	112.00
MAX DIAMETER	21.80	21.80	21.00	21.00	19.80	19.80
MIN DIAMETER	12.50	12.50	12.00	12.00	9.40	9.40
MAX SPHERE	1.00	1.00	1.40	1.40	1.63	1.63
WR ² FOR MAX DIA (LBS-FT ²)	49.00	49.00	52.00	52.00	46.90	46.90
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		3.311	3.311	3.311	3.311	3.311	3.311
DIA THRU SLEEVE		3.311	3.311	3.311	3.311	3.311	3.311
DIA AT COUPLING		3.125	3.125	3.125	3.125	3.125	3.125
SHAFT SPAN - BRG TO BRG		35.80	35.80	35.80	35.80	40.50	40.50
BALL BEARING	INBOARD BRG #	6316	6316	6316	6316	6316	6316
	DIA THRU BRG	3.1502	3.1502	3.1502	3.1502	3.1502	3.1502
	OUTBOARD BRG #	21316	21316	21316	21316	21316	21316
	DIA THRU BRG	3.1502	3.1502	3.1502	3.1502	3.1502	3.1502
FRAME NUMBER		F21-D6	F21-D6	F21-D6	F21-D6	F21-E6	F21-E7
INSTRUCTION BOOK		AC6102	AC6102	AC6102	AC6102	AC6102	AC6102

"H" PREFIX INDICATES HIGH PRESSURE CASING

Supersedes all previous issues

PUMP	SIZE	14x10x20F-L	H14x10x20F-L	16x12x23F
	TYPE	9100	9100	9100
STAGES		1	1	1

CASING DESIGN

FLANGE RATING	SUCTION	125	250	125
	DISCHARGE	125	250	125
CASING MATERIAL		CAST IRON ASTM A48 CLASS 35	DUCTILE IRON ASTM A536 GR 65-45-12	CAST IRON ASTM A48 CLASS 35
MAX DISCHARGE PRESSURE (PSIG)		175	255	175
MAX SUCTION PRESSURE (PSIG)		100	200	100
MAX HYDROSTATIC PRESSURE (PSIG)		262	383	262
CASING WALL THICKNESS		0.62	0.62	0.62

STUFFING BOX DESIGN

BORE	5.12	5.12	5.12
DEPTH	4.81	4.81	4.81
PACKING: # RINGS / SIZE SQUARE	6 / .62	6 / .62	6 / .62
SEAL CAGE WIDTH	0.75	0.75	0.75
SHAFT SLEEVE O.D.	3.88	3.88	3.88

IMPELLER DESIGN

# OF VANES	6	6	6
INLET AREA (IN ²)	129.00	129.00	150.00
MAX DIAMETER	19.80	19.80	23.00
MIN DIAMETER	14.00	14.00	13.00
MAX SPHERE	1.56	1.56	1.63
WR ² FOR MAX DIA (LBS-FT ²)	52.00	52.00	109.00
WEAR RING CLEARANCE - DIAMETRICAL	.015-.017	.015-.017	.015-.017

SHAFT AND BEARING DATA

DIA THRU IMPELLER		3.311	3.311	3.311
DIA THRU SLEEVE		3.311	3.311	3.311
DIA AT COUPLING		3.125	3.125	3.125
SHAFT SPAN - BRG TO BRG		40.50	40.50	40.50
BALL BEARING	INBOARD BRG #	6316	6316	6316
	DIA THRU BRG	3.1502	3.1502	3.1502
	OUTBOARD BRG #	21316	21316	21316
	DIA THRU BRG	3.1502	3.1502	3.1502
FRAME NUMBER		F21-E8	F21-E9	F21-E10
INSTRUCTION BOOK		AC6102	AC6102	AC6102