




Venturi valves

Field adjustable – for all HVAC systems



Bell & Gossett Venturi valves provide balance, ease of commissioning, and shut-off for use in a wide range of HVAC systems. The Venturi design provides efficient and accurate flow balancing with minimal pressure loss. The ball/butterfly valve provides complete shut-off capability for use when servicing a section of your system. Offered in a wide range of sizes and end connections, Bell & Gossett Venturi valves can be the perfect solution for your entire system.

Venturi with ball valve

Brass Venturi flow measurement section with integrated ball valve for small HVAC system applications.

- Calibrated full port ball valve
- Sizes from 1/2" to 2"
- Flow range from 0.3 GPM to 75 GPM
- Memory stop for re-setting valve after Isolation/shut-off
- Integrated P/T ports for easy ΔP measurement
- Union-ended tailpieces for quick installation

Venturi with or without butterfly valve


Steel Venturi flow measurement section with or without butterfly valve for large system applications.

- Available with flange, groove, or weld end connections
- Sizes from 2 1/2" to 12"
- Flow range from 20 GPM to 9,700 GPM
- Integrated 2" P/T ports for easy ΔP measurement
- Flow accuracy as fine as $\pm 1\%$
- Butterfly valve includes 10 position memory stop



Bell & Gossett
xylem

Model MV – Venturi with ball valve dimension information



Body: C37700 brass

Ball: Chrome plated brass

Ball seat: PTFE

O-rings: EPDM

Handle: Chrome plated steel w/vinyl cover

Stem: Explosion proof

Max. working pressure: 400 psig (2,758 kPa)

Temperature range: -4°F (-20°C) to 250°F (121°C)

Accuracy:

+/- 1% between 0.36 psi and 2.53 psi ΔP

+/- 3% between 0.18 & 0.36 psi and 2.53 and 5.42 psi ΔP

+/- 5% for ΔP<0.18 psi and >5.42 psi


See submittal A-606.40 for full pressure drop information.

Size	Flow information in GPM (L/m)		
	Lower flow rate	Upper flow rate	Cv
1/2"L	0.3 (1.1)	0.9 (3.4)	0.55
1/2"H	1.0 (3.8)	4.8 (18.2)	1.6
3/4"UL	0.3 (1.1)	0.9 (3.4)	0.55
3/4"L	1.0 (3.8)	2.8 (10.6)	1.6
3/4"H	3.0 (11.4)	9.0 (34.1)	3.1
1"	2.8 (10.6)	15.0 (56.8)	5
1 1/4"	5.4 (20.5)	26.0 (98.5)	8.8
1 1/2"	12.0 (45.5)	40.0 (151.5)	13
2"	22.0 (83.3)	75.0 (289.1)	24

Size	Dimensions* in inches (mm)		
	A	B	P
1/2"	4.8 (122)	5.5 (140)	2.1 (53)
3/4"	5.2 (132)	6.0 (152)	2.1 (51)
1"	5.7 (148)	6.7 (170)	2.2 (56)
1 1/4"	6.5 (165)	7.5 (190)	2.4 (61)
1 1/2"	8.0 (203)	9.1 (231)	2.7 (68)

*Dimensions not to be used for construction purposes.

Model MVF and VF – Venturi with and without butterfly valve dimension information



Venturi body: Carbon steel

Butterfly valve body: Nodular cast steel

Disc: Aluminum/bronze

Stem: Stainless steel

Liner: EPDM

Max. working pressure: 150 psig (1,034 kPa)

Temperature range:

-4°F (-20°C) to 230°F (111°C) w/o butterfly valve

-4°F (-20°C) to 212°F (100°C) w/butterfly valve

Accuracy:

+/- 1% for ΔP between 0.36 psi and 2.53 psi

+/- 3% for ΔP between 0.18 & 0.36 psi and 2.53 and 5.42 psi

+/- 5% for ΔP<0.18 psi and >5.42 psi

See submittal A-612 for full pressure drop information.

Size	Flow information in GPM (L/m)		
	Lower flow rate	Upper flow rate	Cv
2 1/2"L	20 (76)	140 (530)	45
2 1/2"H	60 (227)	320 (1,211)	97
3"L	30 (114)	220 (833)	69
3"H	80 (303)	580 (2,196)	176
4"L	80 (303)	600 (2,271)	186
4"H	140 (530)	1,000 (3,785)	313
5"	160 (606)	1,250 (4,732)	385
6"	200 (757)	1,500 (5,678)	472
8"	450 (1,703)	2,800 (10,600)	859
10"	600 (2,271)	4,150 (15,710)	1,266
12"	950 (3,596)	9,700 (36,718)	2,941

Size	Dimensions* in inches (mm)				
	A	B	E	G	J
2 1/2"	11.0 (278)	12.8 (324)	6.9 (175)	5/8"	10.5 (267)
3"	11.3 (286)	13.1 (332)	7.1 (180)	5/8"	10.5 (267)
4"	12.7 (321)	14.6 (370)	7.9 (201)	5/8"	10.5 (267)
5"	13.5 (342)	15.7 (398)	8.4 (213)	3/4"	10.5 (267)
6"	15.0 (380)	17.2 (436)	8.9 (226)	3/4"	10.5 (267)
8"	16.9 (427)	19.2 (488)	10.2 (259)	3/4"	***
10"	20.8 (528)	23.4 (594)	11.5 (292)	3/4"	***
12"	26.1 (662)	29.2 (741)	13.3 (338)	3/4"	***

*Dimensions not to be used for construction purposes.

***Denotes gear operated valve.

Xylem product cybersecurity

Xylem values your system security and the availability of your critical services. For more information on Xylem cybersecurity practices or to contact the cybersecurity team please visit [Xylem.com/security](https://www.xylem.com/security).

Xylem Inc.

[xylem.com/bellgossett](https://www.xylem.com/bellgossett)

Subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2026 Xylem Inc. or its affiliate. All rights reserved. Xylem and Bell & Gossett are registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are the property of their respective owners.

A-627C 5/2026

Learn more
about Venturi
valves



xylem
Let's Solve Water