



STAGE	FRAME (3-PHASE) TEFC	HP	L1	L2				D1 (max.)	WEIGHTS (lb)					
				TEFC	L6	L7	L8		M1 (ref.)	TEFC	LIQUID END	TEFC	HYDROVAR	DISCONNECT BOX
1/1	182-4TC	7 1/2	22.19	15.44	6.70	15.52	12.27	6.88	8.50	147	124	10	5	286
1	215TC	10		15.50				8.06	10.25		151			313
2/1	254TC	15	25.19	16.56				18.52	9.25	10.31	158			250

REV	ZONE	ID	DESCRIPTION	REV	ZONE	ID	DESCRIPTION	REV	ZONE	ID	DESCRIPTION

UNITS: INCHES

DO NOT SCALE DRAWING

GENERAL TOLERANCES UNLESS NOTED OTHERWISE:  
 INCHES: X.XX ± .020, X.XXX ± .005  
 MILLIMETERS: XX ± .50, XXX ± .125

ANGLES: ALL ± .5°

GEOMETRIC TOLERANCES IN ACCORDANCE WITH ASME Y14.5M-1994 AND APPLICABLE GOULDS WATER TECHNOLOGY STANDARDS

THIRD ANGLE PROJECTION

PARALLELISM, PERPENDICULARITY, ANGULARITY, TRUE POSITION, RUN OUT, TOTAL RUN OUT (TIR), CONCENTRICITY, FLATNESS, PROFILE

**xylem**  
Let's Solve Water

PART: ELEVATION DRAWING

MODEL(S): HYDROVAR PKG SYS. SIZE(S): 46 SV

DRAWN: BMA DATE: 6/1/09 APPROVED: ES DATE: TBD GROUP:  

CAD: PRO/E DRAWING: B00140C REV:  

PATTERN: MATERIAL: N/A VOLUME: 2413.115 SCALE: 0.100 SHEET: 1 of 1