

## TDC 110 Basic Thermometer with spare battery



### Technical Data

Measurement range	-50 °C ... +150 °C
Resolution	0.1 °C
Measurement accuracy	± 1 °C (-10 °C ... +120 °C), ± 2 °C for the remaining measurement range
Sensor	NTC
Probe needle	Stainless steel, Ø4 mm, L = 120 mm, pointed
Response time (t <sub>99</sub> )	19 sec (water)
Operating temperature	0 °C ... +50 °C
Storage temperature	-10 °C ... +60 °C
Display	7 mm LCD
Battery	1.5 V, G 10-A
Dimensions (L x W)	50 x 40 mm; needle length = 120 mm
Weight	Approximately 13 g

- Automatic shut off after approximately 10 minutes
- Including needle guard

Type	Description	Part No.
TDC 110	Low-Cost Thermometer, incl. needle protection and spare battery	1340-5121

## TDC 150 Basic Thermometer with fast response time



### Technical Data

Measurement range	-50 °C ... +150 °C
Resolution	0.1 °C (-20 °C ... + 150 °C)
Measurement accuracy	± 1 °C (-30 °C ... +150 °C )
Sensor	NTC
Probe	Stainless steel, Ø 3,5 mm, L = 125 mm, pointed
Response time (t <sub>99</sub> )	10 sec (water)
Operating temperature	0 °C ... + 50 °C
Storage temperature	-10 °C ... + 60 °C
Display	LCD-7 mm
Battery	1.5 V LR44, G13
Battery lifetime	Approximately 5.000 h
Dimensions (L x W x H)	24 x 26 x 85 mm
Housing material	ABS

- Approximately 5000 hours battery lifetime
- Waterproof housing (IP 65)
- Including needle protection

Type	Description	Part No.
TDC 150	Thermometer, incl. needle protection	1340-1611