




JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------	----------------------------------------------



1.25AD-es

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

- Stainless Steel Fitted

FEATURES

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- 175 psi (12 bar) W.P.

TYPE OF SEAL


- Standard Seal (Buna-Carbon/Silicon Carbide)
- F Standard Seal w/ Flush Line (Buna-Carbon/Silicon Carbide)

Note: Equipped with NEOPRENE coupling





<p>JOB:</p> <p>UNIT TAG:</p> <p>ENGINEER:</p> <p>CONTRACTOR:</p>	<p>REPRESENTATIVE:</p> <p>ORDER NO.</p> <p>SUBMITTED BY:</p> <p>APPROVED BY:</p>	<p>DATE:</p> <p>DATE:</p> <p>DATE:</p>
-----------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------



1.25AD-es

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

Stainless Steel Fitted

FEATURES

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE


175 psi (12 bar) W.P.

TYPE OF SEAL

- Standard Seal
(Buna-Carbon/Silicon Carbide)
- F Standard Seal w/ Flush Line
(Buna-Carbon/Silicon Carbide)

Note: Equipped with NEOPRENE coupling





NOZZLE SIZES	
Discharge	1-1/4" N.P.T.
Suction	1-1/2" N.P.T.

DIMENSIONS - Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF	HH	HL	HM MAX	HO	HP	Y	Z
	"es" FRAME												
56	12 (305)	28-3/4 (730)	28-3/8 (721)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	3/4 (19)	3-1/8 (79)	13-3/8 (340)	14-3/4 (375)	3 (76)	3-1/4 (83)	4-1/2 (114)
143T	12 (305)	28-3/4 (730)	28-1/2 (724)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	3/4 (19)	3-1/8 (79)	13-1/2 (343)	14-3/4 (375)	3 (76)	3-1/4 (83)	4-1/2 (114)
145T	12 (305)	28-3/4 (730)	29-1/2 (749)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	3/4 (19)	3-1/8 (79)	13-1/2 (343)	14-3/4 (375)	3 (76)	3-1/4 (83)	4-1/2 (114)

Dimensions are subject to change. Not to be used for construction purposes unless certified.



Xylem Inc.
 8200 N. Austin Avenue, Morton Grove, IL 60053
 Phone: (847)966-3700 Fax: (847)965-8379
 www.bellgossett.com
 Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
 © 2016 Xylem Inc.