

# Flygt 2450 HT

50 Hz

## NEW ULTRA HIGH HEAD DEWATERING PUMP

### Denomination

Product code	2450.400
Installation	Portable
Discharge connection	100 mm
Impeller characteristics	High Head Wear Resistant Impellers, Three-Stage Hydraulics

### Process Data

Liquid temperature	40°C (104°F)
Depth of immersion	50 m (164 ft)
Liquid density	1,100 kg/m <sup>3</sup>
Strainer hole dimension	10 x 10 mm
pH of pumped liquid	pH 6-13

### Motor data

Frequency	50 Hz
Insulation Class	H (180°C [360°F])
Voltage Variation	max +/- 10% - intermittent running
Voltage imbalance	max 2% between phases max 30 – no of starts/hour
Rating 50 Hz	140 kW – 2,965 rpm
Rated current (400V)	236 A
Starting current (400V)	2,440 A

### Materials

Impellers	Hard-Iron™
Wear Parts	Hard-Iron™
Stator housing	Cast Iron
Strainer	Galvanized Steel, Stainless Steel
Shaft	Stainless steel
O-rings	Nitrile rubber
Top diffuser	Cast Iron
Inner Mechanical Seal	WCCR Tungsten Carbide
Outer Mechanical Seal	WCCR Tungsten Carbide; RSiC Sil-Carbide

### Weight & dimensions

Installation	Vertical, Horizontal
Weight (excl. cable)	~1,350 kg
Height	1,512 mm
Width	710 mm



**FLYGT**

xylem

# Flygt 2450 HT

50 Hz

## PERFORMANCE CURVE

