



W-23XD Water Quality Sonde

Water quality instrumentation for simultaneously measuring up to 13 different parameters



- Handheld water quality monitoring system with water quality sonde
- Rugged, fully submersible sonde
- Monitor up to 13 different parameters simultaneously
- Dry cell batteries
- Built in datalogger
- Ideal for multi-parameter water quality measurements without having a permanent installation

Description

Global Water's W-23XD water quality sonde brings laboratory accuracy and the ease of push-button operation to water quality instrumentation measurement in the field. Years of water quality instrumentation technology development have resulted in the form of a 97-mm diameter water quality sonde: a compact water quality instrument able to offer high pressure tolerance, long-term continuous measurement capability and highly accurate for the simultaneous monitoring of up to 13 parameters. The water quality sonde can simultaneously measure: pH, temperature, dissolved oxygen, conductivity, salinity, turbidity, total dissolved solids (TDS), water depth, oxidation reduction potential (ORP), seawater specific gravity and up to three specific ions. Featuring a powerful water quality sonde and state-of-the-art functions, the water quality instrumentation makes it easy to get highly reliable water quality data simply and quickly just by submersing the sensor in the water. The water quality sonde is flexible enough to use for checking the quality of a broad range of water samples, from factory effluent to urban drainage, river water, lake and marsh water, aquatic culture tanks, agricultural water supplies, and seawater. The water quality instrumentation is water resistant, so it can be used safely even in the rain.

Specifications

Range:

PH- 0-14 with 0.01 pH resolution and ± 0.1 pH accuracy
DO- 0-20 mg/L with 0.01 resolution and ± 0.2 mg/L accuracy
Conductivity- 0-10 S/m with 0.1% FS res. and $\pm 3\%$ accuracy
Salinity- 0-4% with 0.01% resolution and $\pm 0.3\%$ accuracy
Temp- 0-55°C with 0.01° C resolution and ± 1.0 ° C accuracy
ORP- ± 1999 mV with 1mV resolution and ± 15 mV accuracy
Turbidity- 0-800 NTU with 0.1 NTU res. $\pm 5\%$ accuracy
Seawater Specific Gravity- 0-50 σ t with 0.1 σ t res. and $\pm 5\sigma$ t accuracy
TDS- 0-100 g/L with 0.1% FS resolution and ± 5 g/L accuracy
Water Depth- 0-100 m with 0.1 m res. and $\pm 5\%$ accuracy
Ion- 0.1% FS resolution and $\pm 10\%$ accuracy

Visit www.globalw.com for more specifications

Options and Accessories

W-23XD Water Quality Sonde

Included detachable 2m cable, control unit, sonde, pH and DO sensors, carrying case. ION SENSORS ARE NOT INCLUDED.

Additional cable lengths available for W-23XD, please see our website, www.globalw.com.

ION Sensors

Nitrate
Chloride
Calcium
Fluoride
Potassium
Ammonia

Contact
Global Water
for all your
instrumentation
needs:

Water Level
Water Flow
Water Samplers
Water Quality
Weather
Remote Monitoring
Control



Global Water
a xylem brand

In the U.S. call toll free
at 1-800-876-1172
International: 1-979-690-5560
Fax: 1-979-690-0440
Email: globalw@globalw.com

Visit our online catalog at:
www.globalw.com
Our Address:
11390 Amalgam Way
Gold River, CA 95670