




The Godwin Rig Pump

A RIG-MOUNTED DEWATERING PUMP FOR SAFE, EFFICIENT DEWATERING

SAFE DEWATERING FOR HARSH CONDITIONS


Featuring our Godwin Dri-Prime and Flygt non-clog N-impeller technology



At Xylem, we have been helping companies efficiently dewater sites for over 100 years. We're proud to launch the Godwin Rig Pump, designed to take operational efficiency and safety even further.

Solving challenges - Reduced wear, increased efficiency

Xylem's Godwin Rig Pump solves some of the toughest dewatering challenges in mining by seamlessly integrating with drilling rigs and using state-of-the-art technology. The rig pump lasts up to five times longer than traditional submersible dewatering pumps.



When traditional electrical submersible pumps are used for dewatering mines, they can clog due to shotcrete and wear out due to solids in the water, the pumps can also be left snoring. In addition, mine operators must deal with trailing power cables connecting pumps and must manually move the submersible pumps.

These challenges are solved as the Godwin Rig Pump comes with our famous Dri-Prime self-priming system. By being able to operate in intermittent flows, the rig pump avoids the high wear caused by snoring and has the unique ability to run dry indefinitely.

The rig pump also comes with our leading hard-iron Flygt NC non-clog impeller, enabling it to handle troublesome shotcrete fibers. By avoiding clogging and abrasions, the rig pump helps increase efficiency and uptime. Several different types of pumps can be integrated with the drilling rig to meet your mining conditions and needs.

Traditional Face Dewatering



Drilling rig operators and miners are forced to manually move submersible pumps around the face to dewater the area as well as avoid damage from drill rig movements and rock fall.

Rig Pump Dewatering



The pump is mounted and installed to the drilling rig, which eliminates the safety hazard of pump trailing power cables. Reduces operator and asset exposure at the mine face and allows operator to operate the pump from the safety of the drill rig.



Godwin Rig Pump Operation - Simplicity and Safety

By directly integrating with drilling rigs, the Godwin Rig Pump removes the safety hazard of trailing power cables and allows the operator to operate the pump safely from the rig's cabin. The rig pump also eliminates the need to move submersible pumps, reducing the risks associated with manual handling.



Performance Curve


Pump curve is based on 1m (3.3 ft) dynamic suction lift.



Specifications

Suction connection	100mm (4in) flange
Delivery connection	80mm (3in) flange
Max capacity	160 m³/hr (44l/s) (705 USGPM)
Max impeller diameter	214 mm
Max operating temp	80°C (176°F)
Max pressure	7 Bar (101 psi)
Max suction pressure	2.8 Bar (40 psi)
Max casing pressure	10.5 Bar (152 psi)
Max operating speed	3560 rpm

- Please contact our sales and product support for applications in excess of 80°C (176°F).
- See overview of duty and performance in curve sheet.



Xylem | 'zīlēm|

- 1) The tissue in plants that brings water upward from the roots;
- 2) a leading global water technology company.

We're a global team unified in a common purpose: creating advanced technology solutions to the world's water challenges. Developing new technologies that will improve the way water is used, conserved, and re-used in the future is central to our work. Our products and services move, treat, analyze, monitor and return water to the environment, in public utility, industrial, residential and commercial building services settings. Xylem also provides a leading portfolio of smart metering, network technologies and advanced analytics solutions for water, electric and gas utilities. In more than 150 countries, we have strong, long-standing relationships with customers who know us for our powerful combination of leading product brands and applications expertise with a strong focus on developing comprehensive, sustainable solutions.

For more information on how Xylem can help you, go to www.xylem.com

JOHANNESBURG

TEL: +27 11 966 9300
Email: sales.za@xylem.com
Web: xylem.com/SouthAfrica
Plumbago Business Park,
3A Spier Street, Glen Erasmia,
Kempston Park, South Africa

CAPE TOWN

TEL: +27 21 561 6003
Email: sales.za@xylem.com
Web: xylem.com/SouthAfrica
3 Ruby Road,
North Precinct, Montague Park,
Cape Town, South Africa

RUSTENBURG

TEL: +27 14 596 9680
Email: sales.za@xylem.com
Web: xylem.com/SouthAfrica
Unit 12 Seganka Industrial Park,
89 Ridder Str Rustenburg Industria,
North West Province, South Africa

ALGERIA

TEL: +213 44 76 56 34
Email: res_sales.dz@xylem.com
Web: xylem.com/Algeria
B.P. 02 Route de Batna,
El-Eulma- Wilaya de Sétif

IVORY COAST

TEL: +225 07 69 20 09 00
Email: sales.ci@xylem.com
Web: xylem.com/IvoryCoast
XL Building
Corner of Dr Crozet Street and
Boulevard De La Republique, Plateau
Abidjan, Ivory Coast

EGYPT

TEL: +20 2 2503 2800
Email: sales.eg@xylem.com
Web: xylem.com/Egypt
47 Building, North 90 Street,
New Cairo, Egypt

EGYPT MANUFACTURING

10th of Ramadan City, Industrial Area
A4, Block No. 141, Egypt

KENYA

TEL: +254 743 097 008
Email: sales.ke@xylem.com
Web: xylem.com/Kenya
Garden City Business Park,
Office Block A, 1st floor, Unit 1-A02

MOROCCO

TEL: +212 5377 49943
Email: sales.mr@xylem.com
Web: xylem.com/Morocco
Immeuble Horizon, Mandorana 300,
Lot.9 5ème étage, 20000 Sidi, Maarouf
Casablanca

NIGERIA

TEL: +234 706 119 7707
Email: sales.ng@xylem.com
Web: xylem.com/Nigeria