




GS

Stainless steel submersible pump for 4" and larger wells
60 HZ, 1/2 - 5 HP • VFD compatible – up to 80 HZ



**Engineered, assembled,
and tested in the USA.
You can depend on the
quality and craftsmanship
behind the GS.**

- Premium quality stainless steel internal check valve helps to minimize water loss
- Convenient serviceability: The GS features longer thread engagement in the casing for greater strength and convenient repairs
- Floating stack hydraulic: proven for over 5 decades
- The Guardian System: Includes an engineered polymer bearing which is resistant to damage from sand, abrasives, and over-pumping a well.
- Dual surface upthrust washer providing improved protection to the internal components during upthrust


Applications

- Residential water supply from wells
- Light commercial water systems
- Irrigation systems
- Cisterns and holding tanks
- Livestock watering systems

Water end data

Series	Model	Req. HP	Stages	Length in(mm)	Weight lbs(kg)	Series	Model	Req. HP	Stages	Length in(mm)	Weight lbs(kg)
5GS	5GS05R	0.5	9	12.9 (328)	8 (3.6)	13GS	13GS05	0.5	5	10.1 (257)	6 (2.7)
	5GS05	0.5	12	15.0 (381)	9 (4.1)		13GS07	0.75	7	11.5 (292)	7 (3.2)
	5GS07	0.75	15	17.0 (432)	11 (5.0)		13GS10	1	10	13.6 (345)	8 (3.6)
	5GS10	1	20	21.7 (551)	13 (5.9)		13GS15	1.5	12	15.0 (381)	9 (4.1)
	5GS15	1.5	26	25.8 (655)	15 (6.8)		13GS20	2	17	18.4 (467)	12 (5.4)
	5GS20	2	33	31.6 (803)	19 (8.6)		13GS30	3	21	22.3 (566)	15 (6.8)
7GS	7GS05R	0.5	7	11.7 (297)	6 (2.7)	18GS	18GS07	0.75	6	11.8 (300)	7 (3.2)
	7GS05	0.5	10	13.8 (351)	7 (3.2)		18GS10	1	8	13.5 (343)	8 (3.6)
	7GS07	0.75	13	16.0 (406)	8 (3.6)		18GS15	1.5	11	16.1 (409)	10 (4.5)
	7GS10	1	17	18.8 (478)	9 (4.1)		18GS20	2	14	18.6 (472)	11 (5.0)
	7GS15	1.5	22	23.6 (599)	12 (5.4)		18GS30	3	19	24.1 (612)	15 (6.8)
	7GS20	2	27	27.2 (691)	13 (5.9)		18GS50R	5	24	28.3 (719)	17 (7.7)
	7GS30	3	34	33.2 (843)	18 (8.2)		18GS50	5	30	34.4 (874)	21 (9.5)
10GS	10GS05R	0.5	5	10.1 (310)	6 (3.2)	25GS	25GS10	1	7	13.4 (340)	8 (3.6)
	10GS05	0.5	7	11.5 (345)	7 (3.6)		25GS15	1.5	9	15.3 (389)	9 (4.1)
	10GS07	0.75	10	13.6 (417)	8 (4.1)		25GS20	2	11	17.2 (437)	10 (4.5)
	10GS10	1	12	15.0 (450)	9 (5.0)		25GS30	3	15	20.9 (531)	14 (6.3)
	10GS15	1.5	17	18.4 (467)	12 (5.4)		25GS50R	5	22	28.7 (729)	17 (7.7)
	10GS20	2	20	21.7 (551)	13 (5.9)		25GS50	5	26	33.4 (848)	21 (9.5)
	10GS30	3	27	27.5 (699)	18 (8.2)						
	10GS50R	5	35	33.0 (838)	21 (9.5)						
	10GS50	5	42	40.2 (1021)	24 (10.9)						

Performance curve



Learn more about GS pumps



Xylem Inc.

www.xylem.com/goulds

Subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

©2025 Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are property of their respective owners.

GSSALES R2 7/2025

xylem
Let's Solve Water