



Dimensions and Weights 4SV Series 3500 RPM




Stage	Frame (1-Phase)		Frame (3-Phase)				L2						D1 (max.)		Weights (lb)					
	ODP	TEFC	ODP	TEFC	HP	L1	ODP	TEFC	L3	L5	M1 (ref.)	M2 (ref.)	ODP	TEFC	Liquid End	ODP	TEFC			
2	182-4TC		182-4TC		5	15.75	13.94	15.44		15.75	6.88	6.63	8.50	8.50	33	75	85			
3	213TC				7½	17.25				17.25					35	101	124			
4						18.75				18.75					39					
5			213TC	215TC	10	21.44	15.56	15.50	12.69	21.44	8.06	8.77	10.19	10.25	48	130	151			
6			215TC	254TC	15	24.44		16.56	15.69	24.44	9.25				50	128	250			
7						25.94			17.19	25.94								52		
8						25.94			17.19	25.94									55	
9			254TC	256TC	20	28.88			20.19	28.88					65	220	280			
10						28.88			20.19	28.88								75		
12			256TC		25	31.88							31.88			11.63		79	240	300

Dimensions and Weights 4SV Series 2900 RPM



Stage	Frame (1-Phase)		Frame (3-Phase)		HP	L1	L2		L3	L5	M1 (ref.)	M2 (ref.)	D1 (max.)		Weights (lb)		
	ODP	TEFC	ODP	TEFC			ODP	TEFC					ODP	TEFC	Liquid End	ODP	TEFC
3	182-4TC		182-4TC		3	17.25	13.94	15.44		17.25	6.88	6.63	8.50	8.50	35	75	85
4					5	18.75			11.19	18.75					39	101	124
5	213TC		213TC	215TC	7½	21.44	15.56	15.50	12.69	21.44	8.06	8.77	10.19	10.25	48	130	151
6						24.44			15.69	24.44					50		
7															52		
8			215TC	254TC	10	25.94	15.56	16.56	17.19	25.94	9.25		10.19	10.31	55	128	250
10			254TC	256TC	15	28.88			20.19	28.88					75	220	280
12						31.88				31.88					79		
14						34.88				34.88	13.13		11.63		84		
15			256TC	284TC	20	36.75	18.00	23.38		36.75					86	240	420



Stage	Frame (1-Phase)		Frame (3-Phase)				L2						D1 (max.)		Weights (lb)			
	ODP	TEFC	ODP	TEFC	HP	L1	ODP	TEFC	L3	L5	M1 (max.)	M2 (max.)	ODP	TEFC	Liquid End	ODP	TEFC	
2	Contact Factory		56C		½	15.75	9.16	9.29		15.75	5.06	5.19	6.19		33	24	28	
3					¾	17.25	10.79	9.91		17.25	5.75	5.56			35	32	40	
4					1	18.75	10.66	11.19	11.19						18.75	39	40	43
5					1½	21.44			12.69	21.44					48	43	51	
6						24.44	15.69	24.44					50					
7					2	25.94	11.19	12.06	17.19	25.94			7.19	52				
8														55				
9			182TC	3	28.88	13.94	15.44	20.19	28.88	6.88	6.63	8.50	8.50	65	75	85		
10					31.88				31.88					75				
12					34.88				34.88					79				
14			184TC	5	34.88				34.88					84	101	124		
15					36.75				36.75					86				