



1½ - 3 HP

5 HP is in larger enclosure

FEATURES

Built-in Magnetic Contactors allow the use of standard pressure switches, prolong switch life and eliminate the need to source and install separate contactors, saving installation time and reducing total system component costs.

Voltage Relay for installer convenience

230 volt standard models - 208 volt relay, 9K479 available for low voltage applications

Start Capacitors for starting torque

Run Capacitors for efficiency and quiet operation

Type 3R enclosure for indoor or outdoor mounting

Accepts up to #2 AWG wire

Multiple knockouts and two ground terminals

Manual reset overloads on 1½ - 5 HP models

AGENCY LISTINGS



TESTED TO UL AND CSA STANDARDS BY UL.

Magnetic Contactor 1Ø Control Boxes

FOR 3-WIRE, 1½ - 5 HP SUBMERSIBLE MOTORS

MAGNETIC CONTACTOR (MC) CONTROL BOXES FOR 3 WIRE, 1Ø, 4" GOULDS WATER TECHNOLOGY MOTORS AND 4" (6", 5 HP) FRANKLIN ELECTRIC MOTORS

Control Box Order Number	HP	KW	Volts	Replaces GWT #	Replaces RJ #	May Replace FE #	Standard Circuit Breaker	Standard Fuse	Dual Element Time Delay Fuse	Enclosure Dimensions W x D x H (in)	Shipping Wt. (lbs)
CB15412MC	1.5	1.1	230	No Equal	No Equal	No Equal	30	35	20	8.1 x 5.9 x 9.3	8
CB20412MC	2	1.5	230	00084MC	No Equal	2823018310	25	30	20		
CB30412MC	3	2.2	230	00094MC	S300N1CBC	2823028310	40	45	30		
CB50412MC	5	3.7	230	00104MC	S500N1CBC	2821139310	60	80	45	11 x 6.7 x 12.5	15

"K" REPAIR PARTS FOR MAGNETIC CONTACTOR "MC" CONTROL BOXES

Control Box Order Number	HP	KW	Volts	Capacitor Repair Part Number	Capacitor Type	Capacitor Mfd.	Capacitor Voltage	Capacitor Quantity	Contactor Order Number	Overload Order Number	Start Relay Order Number ①
CB15412MC	1.5	1.1	230	9K447	Start	105-126	250	1	9K485	9K493	9K458
				9K466	Run	15	370				
CB20412MC	2	1.5		9K447	Start	105-126	250			9K480 (S)	
				9K451	Run	20	370			9K472 (M)	
CB30412MC	3	2.2		9K453	Start	208-250	250		9K486	9K473 (S)	9K459
				9K454	Run	45	370			9K474 (M)	
CB50412MC	5	3.7		9K455	Start	270-324	330	1		9K475 (S)	
				9K456	Run	40	370	2		9K476 (M)	

Repair parts above are compatible with and replace parts in Goulds Water Technology or Franklin Electric control boxes.

① If supply voltage is between 200 V - 210 V a 208 V start relay, order no. 9K479, is required.



Xylem Inc.
 2881 East Bayard Street Ext., Suite A
 Seneca Falls, NY 13148
 Phone: (866) 325-4210
 Fax: (888) 322-5877
www.xylem.com/goulds

Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are property of their respective owners.
 © 2023 Xylem Inc. BCMC R4 January 2023