

Rule Slimline submersible and inline pumps

Model	IL200	IL200P	IL200P-24	IL280P	IL280P-24	IL500P	IL500P-24
Voltage VDC	12	12	24	12	24	12	24
Current	2.8A	4.5A	2.5A	4.5A	2.5A	6A	3A
Head height	25 ft. (7.6m)	32 ft. (9.7m)	32 ft. (9.7m)	32 ft. (9.7m)	32 ft. (9.7m)	32 ft. (9.7m)	32 ft. (9.7m)
Flow	200 GPH (760 LPH)	200 GPH (760 LPH)	200 GPH (760 LPH)	280 GPH (1080 LPH)	280 GPH (1080 LPH)	500 GPH (1920 LPH)	500 GPH (1920 LPH)
Continuous duty	No	Yes	Yes	Yes	Yes	Yes	Yes
Outlet	3/8" (10mm) & 1/2" (13mm)	1/2" (13mm)	1/2" (13mm)	1/2" (13mm)	1/2" (13mm)	3/4" (19mm)	1/2" (13mm)
Pressure	11 psi (0.76 bar)	14 psi (0.96 bar)	14 psi (0.96 bar)	14 psi (0.96 bar)	14 psi (0.96 bar)	14 psi (0.96 bar)	14 psi (0.96 bar)
Body	Styrene	Acetal	Acetal	Acetal	Acetal	Acetal	Acetal
Pump Type	Centrifugal	Centrifugal	Centrifugal	Centrifugal	Centrifugal	Centrifugal	Centrifugal
Self priming	No	No	No	No	No	No	No

Rule Slimline submersible and inline pump kits

Kit model number	IL200K	IL280PK	IL280PK-24	IL500PK	IL500PK-24
Flow	200 GPH (760 LPH)	280 GPH (1080 LPH)	280 GPH (1080 LPH)	500 GPH (1920 LPH)	500 GPH (1920 LPH)
Voltage VDC	12	12	24	12	24
Hose	9 ft. (3m) lay flat food quality hose Not for use with diesel	13 ft. (4m) lay flat pvc/nitrite hose	13 ft. (4m) lay flat pvc/nitrite hose	13 ft. (4m) lay flat pvc/nitrite hose	13 ft. (4m) lay flat pvc/nitrite hose