

M420B FlexNet Base Station

Compact Point-to-Multipoint Base Station



Small Footprint

Flexible pole or wall-mounting options enable strategic deployment with a discreet appearance.

Features

- GPS receiver for time synchronization
- Duplexer for single antenna
- IP-addressable power supply with hot-swap capability
- 8-hour battery backup
- Alarms and reporting capability
- Backhaul via Ethernet/IP
- Heated battery for cold weather environments
- Modular construction for easy serviceability

The Sensus FlexNet® M420B Base Station offers a strategic communications option for public service providers with endpoints deployed in remote or densely populated areas.

The efficient transceiver can transmit and receive in a 250kHz band of spectrum. 250kHz enables more dedicated channels, resulting in higher network capacity, allowing more granular data and more channels of data. The Sensus FlexNet communication network delivers eight times the transmit power of competitive systems over primary-use licensed spectrum – ensuring reliability for mission critical applications.

The architecture enables reliable communication of status and usage information with fewer access points than other network architectures. These compact, efficient base stations fit in space-constrained environments and require no air conditioning.

Licensed Radio Spectrum


In North America, FCC/ISED protected primary-use spectrum avoids competition with other wireless services, interference from other radio devices and the risk of being taken over by emergency service providers.

Fewer Access Points

Our point-to-multipoint architecture directly connects base stations to endpoints over large geographic areas – greatly reducing the number of network backhaul connections as well as O&M costs.

Resilient Network Design

Sensus Base Stations continue to provide real time data during outages and emergencies because of eight hour plus battery backup – enabling better workforce management and faster service restoration.



Applications

- Two-way Advanced Meter Infrastructure (AMI)
- Distribution Automation (DA)
- Demand Response (DR)
- Home Area Networks (HAN)
- RNI 4.x or newer
- NCS 2.x
- Unified 3.x
- Micro Grid and Grid Edge

Properties

Receive bandwidth	250 KHz
Transceivers	Single
Spectrum	Licensed 900 MHz PCS/MAS
Duplexing	Thirty-two receivers
Applications	Single
Expandability	No
Compatibility	SNMP
FlexNet	RNI 4.x or newer, Unified 3.x or newer, NCS 2.x or newer

Enclosures - Outdoor - Pole/Wall Mount

Height	22" (55.9 cm)
Width	22" (55.9 cm)
Depth	10.5" (26.7 cm)
Weight	150 lbs. (approx.)
Capacity	One transceiver
Temperature	-40° to +122° F (-40° to +50° C)
Voltage	120 VAC
Battery backup	8 hours
NEMA rating	4
Air conditioned	No

Xylem
639 Davis Drive
Morrisville, NC 27560

Tel +1 800.638.3745
xylem.com

xylem.com/sensus