



Metal iPERL+ Smart Water Meter

Electromagnetic Flow Measurement System

Sensus metal iPERL+® smart water meters are designed to capture both lost water and lost revenue. The innovative magnetic technology delivers unmatched low flow registration and minimal pressure loss. With no moving parts, metal iPERL+ maintains its accuracy over a 20 year lifetime and is equipped with smart water alarms – delivering the intelligence you need to quickly resolve issues in the field.

FEATURES

- 5/8", 5/8" x 3/4", 3/4" and 1" sizes available in potable and reclaim versions.
- 3/4" and 1" available in residential fire service (UL 327b).
- Starts registering flow as low as 0.03 gpm (0.007 m³/hr).
- Can be installed horizontally, vertically or diagonally.
- Compatible with current Sensus AMI/AMR systems.
- Reduces maintenance and cost.
- Allows remote management, monitoring, and diagnosis.
- Logs up to 120 days of hourly consumption data.

BENEFITS

- Maximize investment with iPERL+ electromagnetic technology, which delivers a 20-year accuracy warranty, with no required maintenance, and no loss in accuracy over 20 years.
- Smart alarms detect issues such as continuous flow, high flow, reverse flow, empty pipe, and tampering.
- Improve low flow accuracy to drive additional revenue.

Industry Leading Performance

The patented measurement technology of the metal iPERL+ water meter provides continuous and enhanced accuracy ranges at both low and high flows and perpetual accuracy over the life of the product. The metal iPERL+ meter has a 20-year accuracy warranty and a 20-year battery life guarantee. Over this 20-year lifespan, your metal iPERL+ will measure just as accurately as the day it was installed.

Construction

The metal iPERL+ meter body has a flow tube that is comprised of lead-free bronze alloy with a composite polymer core with an electronic register.

Electronic Register

The 9-digit hermetically-sealed electronic register with LCD display was designed to eliminate dirt, water, and moisture contamination in pit settings. The large, easy-to-read display includes AMI/AMR digits, direction of flow, units of measure, and empty pipe detection. The AMI/AMR digits and units of measure are fully programmable. The register also provides user configurable data logging.

Solid State Electromagnetic Technology

By avoiding the use of a mechanical measuring element inside the flow tube, metering performance is linear over the entire flow range – ensuring no reduction in accuracy at any flow rate over the life of the meter. The iPERL+ meter uses our patented remanent magnetic field technology – requiring far less energy and delivering superior accuracy.

Tamperproof

The integrated construction of the metal iPERL+ water meter prevents removal of the register to obtain free water. The magnetic tamper and low field alarms will both indicate any attempt to tamper with the magnetic field of the metal iPERL+ meter. The meter communication alarm indicates a possible cut cable.

Alarms

Quick resolution of field issues is made possible with smart water alarms including leak detection, reverse flow, empty pipe, magnetic tamper and low battery. When integrated with our FlexNet® communication network, remotely gathering and transmitting data has never been more reliable or profitable.

iPERL+ Smart Water Meter

Electromagnetic Flow Measurement System

Smart Alarms

Metal iPERL meters have many configurable smart alarms designed to protect your utility's investment, enhance customer service, and monitor/optimize distribution systems. These alarms include:


- **High Flow**
Detect large and continuous volume of water. This occurs if the consumption between consecutive reads exceeds the broken pipe threshold.
- **Continuous Flow**
Detect continual consumption of water over a period of time to indicate downstream leaks. This protects your utility, infrastructure and customers through alarm notifications that can reduce water loss and leak adjustment costs.
- **Empty Pipe**
Detects the absence of water in the flow tube and sends an alert. Allows you to identify main breaks downstream and water shortages for quicker resolution to ensure water availability. This alarm can also indicate the water meter has been removed from service, or notify you of potential tamper.
- **Low Battery**
Replace your meters before they stop recording consumption through alerts indicating battery capacity to the meter or valve is running low.
- **Reverse Flow**
Keep untreated water from re-entering your distribution system and deter tampering attempts through an alarm triggered when reverse flow is detected at the meter.
- **Tampering**
Detect magnetic interference to reduce apparent water losses and protect against unauthorized activities.

SPECIFICATIONS

Service	Measurement of potable and reclaim water, and Residential Fire Service (UL 327b). 0-100% humidity. Fully submersible. IP68+ rated.			
Temperature Ranges	Water operating: Ambient air operating: Storage air:	33 °F (0.55 °C) to 80 °F (26.7 °C) -22 °F (-30 °C) to 140 °F (60 °C) -30 °F (-34.4 °C) to 158 °F (70 °C)		
Starting Flow	5/8" (DN 15 mm) size: 0.03 gpm (0.007 m³/h)	5/8" x 3/4" (DN 15x20 mm) size: 0.03 gpm (0.007 m³/h)	3/4" (DN 20 mm) size: 0.03 gpm (0.007 m³/h)	1" (DN 25 mm) size: 0.11 gpm (0.025 m³/h)
Low Flow Range (±3%)	5/8" (DN 15 mm) size: >0.05 gpm (0.011 m³/hr) to <0.18 gpm (0.041 m³/hr)	5/8" x 3/4" (DN 15 mm) size: >0.05 gpm (0.011 m³/hr) to <0.18 gpm (0.041 m³/hr)	3/4" (DN 20 mm) size: >0.05 gpm (0.011 m³/hr) to <0.18 gpm (0.041 m³/hr)	1" (DN 25 mm) size: >0.3 gpm (0.068 m³/hr) to <0.4 gpm (0.09 m³/hr)
Normal Water Operating Flow Range (±1.5%)	5/8" (DN 15 mm) size: 0.18 to 25 gpm (0.04 to 5.7 m³/hr)	5/8" x 3/4" (DN 15x20 mm) size: 0.18 to 35 gpm (0.04 to 8.0 m³/hr)	3/4" (DN 20 mm) size: 0.18 to 35 gpm (0.04 to 8.0 m³/hr)	1" (DN 25 mm) size: 0.4 to 55 gpm (0.09 to 12.5 m³/hr)
Normal Test Flow Limits (per UL 327b Listing, at ±1.5% accuracy)			3/4" (DN 20 mm) size: 2 to 30 gpm (0.5 to 6.8 m³/hr)	1" (DN 25 mm) size: 2 to 50 gpm (0.5 to 11.4 m³/hr)
Maximum Operating Pressure	5/8", 5/8" x 3/4", and 3/4" size: 200 psi (13.8 bar) 1" size: 175 psi (12.1 bar)			
Maximum Operating Pressure (per UL 327b Listing, at ±1.5% accuracy)	3/4" and 1" size: 175 psi (12.1 bar)			
Measurement Technology	Solid state electromagnetic flow			
Register	Hermetically sealed, 9-digit programmable electronic register			
Capacity	10,000,000 gallons, 1,000,000 cubic feet or 100,000 m³ capacity			
Register Resolution	.01 gallons/imperial gallons, .001 cubic foot, or .0001 m³			
Conformance to Standards	Meets the requirements of NSF 61, Annex G and NSF 372. Exceeds the most current revision of AWWA Standard C-715.			
Materials	External housing – Bronze alloy flowtube with a composite polymer internal core		Electrode – Silver/silver chloride Register cover – Hermetically sealed glass	

iPERL+ Smart Water Meter

Electromagnetic Flow Measurement System







DIMENSIONS AND NET WEIGHTS

Meter Size	A	B	C	Spud Ends	NPSM Thread Size	Width	Net Weight
5/8" (DN 15 mm)	7-1/2" (190 mm)	6-1/10" (155mm)	1-3/4" (44 mm)	5/8" (15 mm)	3/4" (20 mm)	4-1/2" (114 mm)	4.9 lb (2.22 kg)
5/8" x 3/4" (DN 15 mm x 20 mm)	7-1/2" (190 mm)	6-1/10" (155mm)	1-3/4" (44 mm)	3/4" (20 mm)	1" (25 mm)	4-1/2" (114 mm)	4.9 lb (2.22 kg)
3/4" Short (DN 20 mm)	7-1/2" (190 mm)	6-1/10" (155 mm)	1-3/4" (44 mm)	3/4" (20 mm)	1" (25 mm)	4-1/2" (114 mm)	5.1 lb (2.31 kg)
3/4" (DN 20 mm)	9" (229 mm)	6-1/10" (155 mm)	1-3/4" (44 mm)	3/4" (20 mm)	1" (25 mm)	4-1/2" (114 mm)	5.2 lb (2.36 kg)
1" (DN 25 mm)	10-3/4" (273 mm)	6-1/10" (155 mm)	1-3/4" (44 mm)	1" (25 mm)	1-1/4" (32 mm)	4-1/2" (114 mm)	5.7 lb (2.59 kg)

iPERL+ Smart Water Meter

Electromagnetic Flow Measurement System

Head Loss Curves



Xylem.com | Sensus.com

SENSUS | 639 Davis Drive | Morrisville, NC 27560 | 800.638.3748

©2024 Sensus. All products purchased and services performed are subject to Sensus' terms of sale, available at either sensus.com/TC or 1-800-638-3748. Sensus reserves the right to modify these terms and conditions in its own discretion without notice to the customer. The Sensus logo is a registered trademark of Sensus.

This document is for informational purposes only, and SENSUS MAKES NO EXPRESS WARRANTIES IN THIS DOCUMENT. FURTHERMORE, THERE ARE NO IMPLIED WARRANTIES, INCLUDING WITHOUT LIMITATION, WARRANTIES AS TO FITNESS FOR A PARTICULAR PURPOSE AND MERCHANTABILITY. ANY USE OF THE PRODUCTS THAT IS NOT SPECIFICALLY PERMITTED HEREIN IS PROHIBITED.