



a xylem brand

YSI TruLab pH 1310 Laboratory Benchtop Meter

Single channel meter for measurement of pH or mV (ORP)

The TruLab® pH 1310 benchtop meter is the ideal laboratory instrument for reliable pH/mV measurements with automatic documentation for GLP compliance. The 1310 is an accurate, easy-to-use solution for the measurement of pH or mv (ORP) in the laboratory. The 1310 has internal memory and is available with or without a built-in printer. Stored data can be sent to a PC via USB or to an optional built-in printer available on the 1310P.



TruLab 1310P

Repeatable/Efficient - the instrument's AutoRead function indicates when a stable measurement is reached improving repeatability.

Convenient/Reliable - data can be printed directly from the instrument via the integrated printer or exported via USB.

Parameters:
pH
mV (ORP/Redox)
Temperature



TruLab 1310

- Single channel measurement of pH, mV (ORP) and temperature.
- Easy-to-read backlit display with text menu for easy operation
- Fast data transfer via USB in .csv or ASCII format or the optional integrated printer
- Continuous Monitoring Control (CMC) function for monitoring the ideal measuring range for pH measurements based on the last calibration
- 1, 2, 3, 4 or 5 point calibration for pH
- 22 stored buffer sets for auto-buffer recognition and easy calibration
- BNC connection for pH, mV; 2 banana connections - 1 for external temperature sensor, 1 for external reference if using a half cell
- 3-year warranty
- GLP/AQA compliant
- Wide selection of electrodes - pH, ORP and temperature probes

TruLab Electrodes

TruLine - single-junction pH electrodes or ORP electrodes. Choice of epoxy or glass body, with temperature compensation or without, flat glass, piercing tip, and refillable or non-refillable.

Science - robust, double-junction pH electrodes available with temperature compensation, with ground or platinum junction.

IoLine - triple-junction pH electrodes with Iodine/Iodide reference for specialized applications, refillable with temperature compensation.

TruLab pH 1310 Instrument Specifications

	Range	Resolutions	Accuracy (± 1 digit)
pH	-2.0 to 20.0; -2.00 to 20.00; -2.000 to 19.999	0.1; 0.01; 0.001	± 0.1 ; ± 0.01 ; ± 0.005 (temp of test sample 15 to 35°C; within a range of ± 2 pH of the calibration point)
mV	-1200 to 1200.0; -2500 to 2500	0.1; 1.0	± 0.3 ; ± 1.0 (temp of test sample 15 to 35°C)
Temperature	-5 to 105 °C (23.0 to 221 °F)	0.1	± 0.1

TruLab pH 1310 & pH1310P Additional Specifications

Power Supply	4 alkaline AA batteries (~150 hours with illumination, 1000 without); universal power supply; compatible with 4 NiMH AA rechargeables*			
Manual Temperature Input	-25 to 130°C (-13 to 266°F) in increments of 1			
Display	Backlit graphic display			
Memory	5,000 data sets auto logging; 500 data sets manual logging			
Calibration	1, 2, 3, 4 or 5 points			
Storage	-25 to 65°C (-13 to 149°F)			
Weight	1310	0.8 kg (1.8 lbs)	1310P	1.0 kg (2.0 lbs)
Dimensions	1310	230 L x 190 W x 80 H mm (9.0 x 7.5 x 3.2 in)	1310P	280 L x 230 W x 80 H mm (11 x 9.0 x 3.2 in)
Certifications	CE, cETLus; electrical protective class III; IP43			
Warranty	3 years			

Ordering Information

1AA320Y	TruLab pH1310 pH/mV benchtop meter with BNC single channel input, data storage and USB data transfer. Includes universal power supply, stand, manual, software and USB cable.
1AA320PY	TruLab pH1310P pH/mV benchtop meter with BNC single channel input, data storage, USB data transfer and integrated thermal printer. Includes universal power supply, stand, manual, software and USB cable.
400350	TruLine pH15; pH electrode with temperature, single-junction, 3 in 1, refillable, glass shaft with 1-m cable, BNC connector, 1 banana plug, NTC 30 kOhm. Dimensions = 120 mm length; 12 mm OD
400351	TruLine pH 17; pH electrode no temperature, single-junction, combination, refillable, glass shaft with 1-m cable, BNC connector. Dimensions = 120 mm length; 12 mm OD
400352	TruLine pH 26; pH electrode with temperature, single-junction, 3 in 1, gel electrolyte, epoxy shaft with 1-m cable, BNC connector, 1 banana plug, NTC 30 kOhm. Dimensions = 120 mm length; 12 mm OD
400353	TruLine pH 25; pH electrode no temperature, single-junction, combination, gel electrolyte, epoxy shaft with 1-m cable, BNC connector. Dimensions = 120 mm length; 12 mm OD
400354	TruLine pH 27; pH electrode no temperature, single-junction, combination, flat glass membrane for surface measurements, glass shaft with 1-m cable, BNC connector. Dimensions = 120 mm length; 12 mm OD
400355	TruLine ORP 50; ORP electrode no temperature, single-junction, refillable, glass shaft with 1-m cable, BNC connector. Dimensions = 120 mm length; 12 mm OD
400356	TruLine ORP 51; ORP electrode no temperature, single-junction, gel electrolyte, epoxy shaft with 1-m cable, BNC connector. Dimensions = 120 mm length; 12 mm OD
400357	TruLine pH 21; pH electrode no temperature, single-junction, combination, spear tip membrane, epoxy shaft with 1-m cable, BNC connector. Dimensions = tapered to spear tip
400358	IoLine - 3 in 1; pH electrode with temperature, triple-junction, Iodine/Iodide reference, 3 in 1, refillable, glass shaft with 1-m cable, BNC connector, 1 banana plug, NTC 30 kOhm. Dimensions = 120 mm length; 12 mm OD
400359	IoLine Micro - 3 in 1; pH electrode with temperature, triple-junction, Iodine/Iodide reference, 3 in 1, refillable, Micro electrode, glass shaft with 1-m cable, BNC connector, 1 banana plug, NTC 30 kOhm. Dimensions = 200 mm overall length (tapered); 12 mm OD to 6 mm OD (tapered)
400360	Science pH-T-Pt; pH electrode with temperature, double-junction, Platinum junction, 3 in 1, glass shaft with 1-m cable, BNC connector, 1 banana plug, NTC 30 kOhm. Dimensions = 170 mm length; 12 mm OD
400361	Science pH-T-G; pH electrode with temperature, double-junction, 3 in 1, ground joint junction, glass shaft with 1-m cable, BNC connector, 1 banana plug, NTC 30 kOhm. Dimensions = 170 mm length; 12 mm OD
400362	Science pH-T-Micro; pH electrode with temperature, double-junction, 3 in 1, Platinum junction, Micro electrode, glass shaft with 1-m cable, BNC connector, 1 banana plug, NTC 30 kOhm. Dimensions = 200 mm overall length (tapered); 12 mm OD to 5 mm OD (tapered)
400363	ScienceLine Temp 135; temperature sensor, stainless steel, 1 banana plug, NTC 30 kOhm. Dimensions = 120 mm length; 4 mm OD
400364	ScienceLine Temp 136; temperature sensor, glass, 1 banana plug, NTC 30 kOhm. Dimensions = 120 mm length; 6 mm OD

* Instrument will not charge the rechargeable batteries

YSI

1725 Brannum Lane, Yellow Springs, OH 45387

Tel +1 937.767.7241 800.897.4151 (US)

environmental@ysi.com

YSI.com @YSIinc facebook.com/myYSI

YSI and TruLab are registered trademarks.

Specifications are subject to change. Please visit YSI.com to verify all specs.

©2014 YSI, a xylem brand

Printed in the USA. W72 0314



a xylem brand