




Air Pressure Sensor 2810A/2810A Ex

A barometric pressure sensor produced for use in hot climates and designed for Aanderaa Automatic Weather Stations and Display Units.



The monolithic technology used in modern electronic devices may also be used for making small pressure sensors. Sensors made using this method have very small hysteresis and a very low rate of ageing.

To eliminate error due to ambient temperature changes the small sensing element can be heated to a specific temperature before the measurement is taken.

Air Pressure sensor 2810 utilizes a 4x4mm small silicon chip as a sensing element. In the central area of this chip is a thin membrane that is exposed to atmospheric pressure on one side and to a vacuum on the other. The membrane is furnished with 4 diffused resistors that form a Wheatstone bridge. The output signal is proportional to the atmospheric pressure. The chip thus acts as an absolute pressure-sensing device.

A temperature sensing resistor and 4 heating resistors are also diffused onto the chip. In conjunction with an external control circuit, these resistors allow the chip to be held at a constant temperature of 60°C during the measurement.


The sensor consists of a PC-board with components fastened to the sensor base and protected by a cylindrical cover. The cover is screwed onto the base and sealed with an O-ring. Six holes in the base provide atmospheric pressure to the sensing element inside the sensor.

The sensor shows outstanding performance as it has practically no hysteresis, no temperature drift and no ageing. It is also insensitive to mechanical acceleration and can be operated in any position. The sensor is waterproof.

Before measurement the sensor is heated to 60°C and to allow enough time for temperature stabilization the sensor should be connected to one of the last channels in the measuring system.

Current consumption for silicon chip heating varies with ambient temperature. At 60°C the heating current is zero. This increases linearly as temperature decreases. A maximum of 70 mA for heating is reached at -40°C. The heating current is normally switched off between readings.

Specifications 2810A/2810A Ex



PIN CONFIGURATION

Receptacle, exterior view, bushing = ○; pin = ●

Bridge ground	6	1	System ground
Signal	5	2	-6 volts
Bridge voltage	4	3	-9 volts

The sensor is also available as an -certified sensor; contact factory for prices.

Measuring Range: 920 - 1080hPa¹⁾ (other ranges on request)..... hPa

Accuracy: ±0.2 hPa

Resolution: 0.2 hPa

Operation Temp. Range: -40 to +60°C

Sensor Output: Aanderaa half-bridge, VR22

Supply Voltage: 7-14VDC (9 volt nominal)

Current Consumption: 5mA + heating: (60-T) 0.75mA
T=ambient temperature in °C

Electrical Connection: Automatic Weather Station (AWS)
Sensor Arm or Sensor Cable

Material and Finish: Aluminum 6061-T6, anodized 10μ

Weight: 200 grams

Packing: Cardboard box

Gross Weight: 400 grams

Warranty: Two years against faulty materials and workmanship certified

¹⁾ The standard range can be used up to an installation altitude of approximately 400 meters. For higher altitudes the range must be set by the factory prior to delivery.

To refer the measured air pressure to sea level add a factor according to the table below (approx.value):

Installation altitude (m)	Add 1hPa each	Installation altitude (m)	Add 1hPa each
0 - 200	8m	801 - 1000	9m
201 - 400	8.5m	1001 - 2000	9.6m
401 - 600	8.7m	2001 - 3000	10.7m
601 - 800	8.9m	3001 - 5000	12.4m



Visit our Web site for the latest version of this document and more information
www.aanderaa.com

Aanderaa is a trademark of Xylem Inc. or one of its subsidiaries.
© 2012 Xylem, Inc. D161A May 2015

Aanderaa Data Instruments AS
Sanddalsringen 5b, P.O. Box 103 Midtun,
5828 Bergen, Norway
Tel +47 55 60 48 00
Fax +47 55 60 48 01