



Jabsco Marine Toilets

SIMPLY RELIABLE SOLUTIONS FOR EVERY BOAT AND BUDGET



a xylem brand



From best-selling manual toilets to household-style luxury models, our marine toilets are both simple and reliable.

- All toilet models have hygienic, pure white vitreous china bowls that are attractive and easy to clean.
- A wooden seat and lid with a baked enamel finish and standard close hinges also comes standard on all toilet models except the Lite Flush.
- A luxury composite seat and lid comes standard on the Lite Flush, and is an option on all other toilet models with regular size bowls. It's made of Duroplast, a high performance material designed to look and feel like ceramic with an anti-scratch surface for increased hygiene, and features a soft close hinge system.
- All electric toilets comply with USCG 183.410 and ISO 8846 MARINE (Ignition Protection).

Jabco is the world's largest manufacturer and supplier of small craft marine toilets. All our toilets can be used on inland waterways, rivers, lakes or the sea. All can be installed above or below the waterline. All can discharge overboard or into holding tanks. Learn more about our models and options at: marine.xylem.com

Toilet Systems

Twist 'n' Lock Manual Toilet

Popular worldwide for more than two decades, Jabsco's sturdy manual toilet ensures peace of mind thanks to the intuitive, simple to use Twist 'n' Lock feature. It provides protection against siphonic flooding and waste backflow with one easy, 90° turn of a handle. The toilet is available with a regular or compact size bowl.

- A powerful self-priming pump allows installation above or below the waterline.
- A reversible mounting gives the option to install the pump on the right or left.
- A flexible design makes it suitable for either overboard or holding tank discharge.
- Corrosion-resistant materials throughout permit salt and fresh water service.
- Fastenings face front or top for ease of maintenance.
- For use with sea, river or lake water only.

PART NUMBER	DESCRIPTION	REPLACES MODEL	BOWL SIZE	SEAT & LID	RINSE TYPE	RINSE PUMP/ SOLENOID VALVE
29090-5000	Manual Toilet	29090-3000	Compact	Wood - Standard Close	Raw Water	–
29120-5000	Manual Toilet	29120-3000	Regular	Wood - Standard Close	Raw Water	–
29120-5100	Manual Toilet	–	Regular	Composite - Soft Close	Raw Water	–



VOLTAGE DC	RECOMMENDED FUSE SIZE (AMP)	FLUSH CONTROL SWITCH	HEIGHT INCH (mm)	WIDTH INCH (mm)	DEPTH INCH (mm)	WEIGHT LBS (kg)
–	–	Manual Pump	12.9 (330)	17.5 (445)	16.7 (425)	24.3 (11)
–	–	Manual Pump	13.8 (350)	18.5 (470)	19.1 (485)	28.7 (13)
–	–	Manual Pump	13.8 (350)	18.5 (470)	19.1 (485)	28.7 (13)

Toilet Systems

Electric Toilet

This versatile toilet brings the luxury of electric flushing aboard your vessel. It offers two options: a household size bowl for all the convenience of home, and a compact bowl where space is a premium.

- An integral self-priming rinse pump designed to bring sea, river or lake water into the bowl comes standard.
- A flexible design makes it suitable for overboard or holding tank discharge.
- A built-in backflow preventer guards against flooding and waste return.
- Corrosion-resistant materials throughout permit fresh or salt water service.
- Can be mounted 3' (1m) above or below the waterline with appropriate plumbing.
- For use with sea, river or lake water only.

PART NUMBER	DESCRIPTION	REPLACES MODEL	BOWL SIZE	SEAT & LID	RINSE TYPE	RINSE PUMP/ SOLENOID VALVE
37010-3092	Electric Toilet	37010-0090	Compact	Wood - Standard Close	Raw Water	Integral Rinse Pump
37010-3094	Electric Toilet	37010-0096	Compact	Wood - Standard Close	Raw Water	Integral Rinse Pump
37010-4092	Electric Toilet	37010-1092	Regular	Wood - Standard Close	Raw Water	Integral Rinse Pump
37010-4094	Electric Toilet	37010-1096	Regular	Wood - Standard Close	Raw Water	Integral Rinse Pump
37010-4192	Electric Toilet	–	Regular	Composite - Soft Close	Raw Water	Integral Rinse Pump
37010-4194	Electric Toilet	–	Regular	Composite - Soft Close	Raw Water	Integral Rinse Pump



VOLTAGE DC	RECOMMENDED FUSE SIZE (AMP)	FLUSH CONTROL SWITCH	HEIGHT INCH (mm)	WIDTH INCH (mm)	DEPTH INCH (mm)	WEIGHT LBS (kg)
12	25	Single Button Panel	13.2 (335)	13.9 (352)	17.7 (450)	34.2 (15.5)
24	15	Single Button Panel	13.2 (335)	13.9 (352)	17.7 (450)	34.2 (15.5)
12	25	Single Button Panel	14.4 (365)	14.8 (375)	19.1 (485)	38.6 (17.5)
24	15	Single Button Panel	14.4 (365)	14.8 (375)	19.1 (485)	38.6 (17.5)
12	25	Single Button Panel	14.0 (355)	14.8 (375)	19.1 (485)	38.6 (17.5)
24	15	Single Button Panel	14.0 (355)	14.8 (375)	19.1 (485)	38.6 (17.5)

Toilet Systems

Quiet Flush Electric Toilet

Based on our proven Electric Toilet, the Quiet Flush is designed to radically reduce noise levels, making life more comfortable for everyone onboard – even those sleeping. It's available in two versions: one that connects to a vessel's existing pressurized water system, or one with a remote mounted pump to use sea, river or lake water to flush.

- Models designed for boats with onboard pressurized water systems capable of delivering 2.9 GPM (11 LPM) or more have a solenoid valve assembly that includes an anti-siphon breaker to ensure no backflow from the toilet into the water system.
- Models designed for boats without adequate pressurized water systems feature a remote mounted, self-priming rinse pump that brings in sea, river or lake water for flushing, and includes a pump guard strainer.
- A powerful macerating discharge pump breaks up waste while evacuating the toilet.
- A control panel allows three different water levels for flush and drain cycles.
- Regular and compact size bowls are available.
- Can be mounted 3' (1m) above or below the waterline with appropriate plumbing.

PART NUMBER	DESCRIPTION	REPLACES MODEL	BOWL SIZE	SEAT & LID	RINSE TYPE	RINSE PUMP/ SOLENOID VALVE
37045-3092	Quiet Flush Toilet	37045-0092	Compact	Wood - Standard Close	Fresh Water	Solenoid Valve
37045-3094	Quiet Flush Toilet	37045-0094	Compact	Wood - Standard Close	Fresh Water	Solenoid Valve
37045-4092	Quiet Flush Toilet	37045-1092	Regular	Wood - Standard Close	Fresh Water	Solenoid Valve
37045-4094	Quiet Flush Toilet	37045-1094	Regular	Wood - Standard Close	Fresh Water	Solenoid Valve
37045-4192	Quiet Flush Toilet	–	Regular	Composite - Soft Close	Fresh Water	Solenoid Valve
37045-4194	Quiet Flush Toilet	–	Regular	Composite - Soft Close	Fresh Water	Solenoid Valve
37245-3092	Quiet Flush Toilet	37245-0092	Compact	Wood - Standard Close	Raw Water	Remote Rinse Pump
37245-3094	Quiet Flush Toilet	37245-0094	Compact	Wood - Standard Close	Raw Water	Remote Rinse Pump
37245-4092	Quiet Flush Toilet	37245-1092	Regular	Wood - Standard Close	Raw Water	Remote Rinse Pump
37245-4094	Quiet Flush Toilet	37245-1094	Regular	Wood - Standard Close	Raw Water	Remote Rinse Pump
37245-4192	Quiet Flush Toilet	–	Regular	Composite - Soft Close	Raw Water	Remote Rinse Pump
37245-4194	Quiet Flush Toilet	–	Regular	Composite - Soft Close	Raw Water	Remote Rinse Pump



VOLTAGE DC	RECOMMENDED FUSE SIZE (AMP)	FLUSH CONTROL SWITCH	HEIGHT INCH (mm)	WIDTH INCH (mm)	DEPTH INCH (mm)	WEIGHT LBS (kg)
12	25	Dual Rocker Panel	14.0 (355)	13.9 (352)	16.3 (415)	34.2 (15.5)
24	15	Dual Rocker Panel	14.0 (355)	13.9 (352)	16.3 (415)	34.2 (15.5)
12	25	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)
24	15	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)
12	25	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)
24	15	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)
12	25	Dual Rocker Panel	14.0 (355)	13.9 (352)	16.3 (415)	34.2 (15.5)
24	15	Dual Rocker Panel	14.0 (355)	13.9 (352)	16.3 (415)	34.2 (15.5)
12	25	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)
24	15	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)
12	25	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)
24	15	Dual Rocker Panel	14.4 (365)	14.8 (375)	18.9 (480)	38.6 (17.5)

Toilet Systems

Deluxe Flush Electric Toilet

Our top-of-the-line electric toilet, the Deluxe Flush, is designed to conceal the flush pump, wiring and plumbing, while featuring a full-size household seat. It's available in 14" or 17" models, both with the choice of a straight or slanted back. The straight back version fits snugly against a vertical bulkhead, while the slant back version mounts against a slope or in a corner, giving it a smaller footprint.

- Specially designed pumps and components mean virtually silent operation.
- A powerful, anti-blocking centrifugal flush pump.
- Models offer a choice between flushing with external water or connecting to an existing pressurized water source.
- Models designed for boats with onboard pressurized water systems capable of delivering 2.9 GPM (11 LPM) or more have a solenoid valve assembly that includes an anti-siphon breaker to ensure no backflow from the toilet into the water system.
- Models designed for boats without adequate pressurized water systems feature a remote mounted, self-priming rinse pump that brings in sea, river or lake water for flushing, and includes a pump guard strainer.
- Four rinse options allow for minimum water usage of 1.5 US quarts (1.5 L).
- The multifunctional control pad adapts to standard Gewiss and Vimar switch fascias.

PART NUMBER	DESCRIPTION	REPLACES MODEL	BOWL SIZE	SEAT & LID	RINSE TYPE	RINSE PUMP/ SOLENOID VALVE
58040-2012	Deluxe Flush Toilet 17" Straight	58040-1012	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58040-2024	Deluxe Flush Toilet 17" Straight	58040-1024	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58040-3012	Deluxe Flush Toilet 17" Straight	–	Domestic	Composite - Soft Close	Fresh Water	Solenoid Valve
58040-3024	Deluxe Flush Toilet 17" Straight	–	Domestic	Composite - Soft Close	Fresh Water	Solenoid Valve
58240-2012	Deluxe Flush Toilet 17" Straight	58240-1012	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump
58240-2024	Deluxe Flush Toilet 17" Straight	58240-1024	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump
58240-3012	Deluxe Flush Toilet 17" Straight	–	Domestic	Composite - Soft Close	Raw Water	Remote Rinse Pump
58240-3024	Deluxe Flush Toilet 17" Straight	–	Domestic	Composite - Soft Close	Raw Water	Remote Rinse Pump
58020-1012	Deluxe Flush Toilet 17" Angled	–	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58020-1024	Deluxe Flush Toilet 17" Angled	–	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58220-1012	Deluxe Flush Toilet 17" Angled	–	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump
58220-1024	Deluxe Flush Toilet 17" Angled	–	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump
58080-1012	Deluxe Flush Toilet 14" Straight	–	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58080-1024	Deluxe Flush Toilet 14" Straight	–	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58280-1012	Deluxe Flush Toilet 14" Straight	–	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump
58280-1024	Deluxe Flush Toilet 14" Straight	–	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump
58060-1012	Deluxe Flush Toilet 14" Angled	–	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58060-1024	Deluxe Flush Toilet 14" Angled	–	Domestic	Wood - Standard Close	Fresh Water	Solenoid Valve
58260-1012	Deluxe Flush Toilet 14" Angled	–	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump
58260-1024	Deluxe Flush Toilet 14" Angled	–	Domestic	Wood - Standard Close	Raw Water	Remote Rinse Pump



VOLTAGE DC	RECOMMENDED FUSE SIZE (AMP)	FLUSH CONTROL SWITCH	HEIGHT INCH (mm)	WIDTH INCH (mm)	DEPTH INCH (mm)	WEIGHT LBS (kg)
12	25	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	63.9 (29)
24	15	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	63.9 (29)
12	25	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	63.9 (29)
24	15	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	63.9 (29)
12	25	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	68.3 (31)
24	15	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	68.3 (31)
12	25	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	68.3 (31)
24	15	4 Button Touch Panel	17.5 (445)	14.8 (375)	18.7 (475)	68.3 (31)
12	25	4 Button Touch Panel	17.5 (445)	14.8 (375)	17.7 (450)	61.7 (28)
24	15	4 Button Touch Panel	17.5 (445)	14.8 (375)	17.7 (450)	61.7 (28)
12	25	4 Button Touch Panel	17.5 (445)	14.8 (375)	17.7 (450)	66.1 (30)
24	15	4 Button Touch Panel	17.5 (445)	14.8 (375)	17.7 (450)	66.1 (30)
12	25	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	55.1 (25)
24	15	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	55.1 (25)
12	25	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	55.1 (25)
24	15	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	59.5 (27)
12	25	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	59.5 (24)
24	15	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	59.5 (24)
12	25	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	57.3 (26)
24	15	4 Button Touch Panel	14.4 (366)	14.8 (375)	17.7 (450)	57.3 (26)

Toilet Systems

Lite Flush Toilet

Designed to instantly retrofit Jabsco manual toilets, the Lite Flush uses the same footprint, fixing points and hose attachments, making installation quick and straightforward. Stylish, compact, lightweight and quiet, its flush and rinse pump system consumes very little power and uses very little water. Models feature either a left or right fitting foot switch or a one-touch wall mounted control panel for flushing.

- The design makes it easy to upgrade an existing manual toilet to electric.
- Powerful centrifugal flush pump to evacuate waste.
- An integral self-priming rinse pump designed to bring sea, river or lake water into the bowl.
- The self-contained rinse and flush pump system is energy efficient.
- Water usage is as low as 1.3 US quarts (1.2 L) per flush.
- A ceramic bowl and plastic outer casing make it lightweight and easy to clean.
- Slow close seat and lid.
- For use with sea, river or lake water only.

PART NUMBER	DESCRIPTION	REPLACES MODEL	BOWL SIZE	SEAT & LID	RINSE TYPE	RINSE PUMP/ SOLENOID VALVE
58500-0012	Lite Flush Toilet	–	Compact	Composite - Soft Close	Raw Water	Integral Rinse Pump
58500-1012	Lite Flush Toilet	–	Compact	Composite - Soft Close	Raw Water	Integral Rinse Pump
58500-0024	Lite Flush Toilet	–	Compact	Composite - Soft Close	Raw Water	Integral Rinse Pump
58500-1024	Lite Flush Toilet	–	Compact	Composite - Soft Close	Raw Water	Integral Rinse Pump



VOLTAGE DC	RECOMMENDED FUSE SIZE (AMP)	FLUSH CONTROL SWITCH	HEIGHT INCH (mm)	WIDTH INCH (mm)	DEPTH INCH (mm)	WEIGHT LBS (kg)
12	25	Foot Switch	14.7 (373)	15.8 (401)	15.8 (401)	24.3 (11)
12	15	2 Button Touch Panel	14.7 (373)	15.8 (401)	15.8 (401)	24.3 (11)
24	25	Foot Switch	14.7 (373)	15.8 (401)	15.8 (401)	24.3 (11)
24	15	2 Button Touch Panel	14.7 (373)	15.8 (401)	15.8 (401)	24.3 (11)

Accessories & Pumps

Outlet Non-Return Valve

This valve, which easily fits to the discharge hose, helps prevent waste backflow on electric toilets.



MODEL NUMBER	DESCRIPTION
58109-1000	1-1/2" (38mm) Outlet Non-Return Joker Valve

Y-Valve

This robust Y-valve provides the option to pump waste overboard or into a holding tank. It features rotating ports for variable routing of hoses, and can be operated through the bulkhead by the use of an optional handle extension. Valve can be padlocked to comply with some local regulations (padlock not included).



SPECIFICATIONS

Fitting:	Connections for two 1-1/2" (38mm) ports and 1" (25mm) inlet port
Size:	7-5/8" long x 7-1/4" wide x 4-5/8" high (20cm x 19cm x 12cm)
Weight:	2lb (0.9kg)

MODEL NUMBER	DESCRIPTION
45490-1000	Y-Valve
45500-1000	Handle Extension Kit
45493-0000	Replacement Handle
18753-0661	Replacement Ports Kit
45488-0000	Service Kit

Inlet Non-Return Valve

This valve improves the flushing response on manual and electric toilets that use sea water flush. It also prevents the loss of prime in above-waterline installations.



SPECIFICATIONS

Fitting:	Connections for 3/4" (19mm) ID hose
Size:	4-1/4" long x 2-1/8" wide x 2" high (10.8cm x 5.5cm x 5cm)
Weight:	0.25lb (0.1kg)

MODEL NUMBER	DESCRIPTION
29295-1011	Inlet Non-Return Valve

Vented Loops

This is an essential safety component on toilets installed below the static or heeled waterline. Its simple valve system ensures that water won't siphon over plumbing loops. Plus, it eliminates the need for external venting. Molded in tough, corrosion-proof plastic, it's available in three sizes: for 1-1/2" (38mm), 1" (25mm) and 3/4" (19mm) ID hose.



SPECIFICATIONS

Fitting:	Connections for 3/4" (19mm), 1" (25mm) and 1-1/2" (38mm) ID hose
Size:	3/4" (19mm) Model: 3" high x 3-3/4" wide x 1" deep (7.5cm x 9.5cm x 2.5cm) 1" (25mm) Model: 5" high x 7-1/2" wide x 1-3/4" deep (12.5cm x 19cm x 4.5cm) 1-1/2" (38mm) Model: 5" high x 7-1/4" wide x 2" deep (12.5cm x 18.5cm x 5cm)
Weight:	3/4" (19mm) Model: 1.5oz (0.04kg) 1" (25mm) Model: 0.25lb (0.13kg) 1-1/2" (38mm) Model: 0.5lb (0.2kg)

MODEL NUMBER	DESCRIPTION
29015-0000	3/4" (19mm) Model
29015-0020	1" (25mm) Model
29015-0010	1-1/2" (38mm) Model
29015-1000	Replacement valve. Only available in Europe.

Toilet Pumpgard™

The Pumpgard protects manual or electric toilets from pump malfunctions caused by debris. Easily installed in a 3/4" (19mm) ID inlet hose, it features a transparent housing that allows instant inspection and a screw-off top for quick, in-place cleaning and debris removal.



SPECIFICATIONS

Fitting: Connections for 3/4" (19mm) ID hose

Size: 4-3/4" long x 2-3/4" wide x 2-1/2" high
(12cm x 7cm x 6cm)

MODEL NUMBER	DESCRIPTION
46400-0000	Toilet Pumpgard™
18753-0040	Replacement 40# Mesh Filter

Waste Pump

With a robust diaphragm and a 5 GPM (19 LPM) output, this pump is extremely efficient at passing solids, and is particularly effective in emptying holding tanks. Self-priming up to 10' (3m), it runs quietly and is capable of extensive dry running. The multi-positional pump head offers a variety of installation options. It complies with USCG 183.410, ISO 8846 MARINE (Ignition Protection) and ISO 8849 MARINE (Bilge Pump Standard).



SPECIFICATIONS

Fitting: Connections for 1-1/2" (38mm) ID hose

Size: 10.9" long x 6.1" wide x 4.4" high
(27.7cm x 15.5cm x 11.1cm)

Weight: 6lb (2.7kg)

MODEL NUMBER	DESCRIPTION
50890-1000	12V DC, Fuse 10 amp
50890-1100	24V DC, Fuse 5 amp
SK890	Service Kit

Run-Dry Macerator Waste Pump

A fully sealed motor and a powerful four-bladed chopper virtually eliminate the possibility of clogging when running this pump. The sealed motor consists of O-ring sealed endbells, sealed bearings, and a hard, durable powder coating to prevent corrosion internally and externally. It includes the Run-Dry feature, which shuts off the pump when it senses an absence of fluid. Self-priming to 4' (1.2m) vertical lift, it has a flow rate of 12 GPM (45 LPM). It complies with USCG 183.410 and ISO 8846 MARINE (Ignition Protection).



SPECIFICATIONS

Fitting: Connections for 1-1/2" (38mm) ID hose

Size: 10.9" long x 6.1" wide x 4.4" high
(27.7cm x 15.5cm x 11.1cm)

Weight: 6lb (2.7kg)

MODEL NUMBER	DESCRIPTION
18590-2092	12V DC Pump, Marine Model
18590-2094	24V DC Pump, Marine Model
17288-1000	Replacement Bolt Kit
18598-1000	Service Kit

Waste Tank

This rugged polyethylene holding tank has a 10 gallon (38 litre) capacity. It allows for dockside pump-out pick-up, and features convenient mounting points. Its heavy-duty self-priming macerator evacuation pump has a 12 GPM (45 LPM) flow rate and an integral run-dry protection device. A waste management control panel empties the tank at the touch of a button.



MODEL NUMBER	DESCRIPTION
38110-0092	Waste Management System - 10 Gallon (38L) - 12V DC
38110-0094	Waste Management System - 10 Gallon (38L) - 24V DC

Xylem |'zīləm|

- 1) The tissue in plants that brings water upward from the roots;
- 2) a leading global water technology company.

We're a global team unified in a common purpose: creating innovative solutions to meet our world's water needs. Developing new technologies that will improve the way water is used, conserved, and re-used in the future is central to our work. We move, treat, analyze, and return water to the environment, and we help people use water efficiently, in their homes, buildings, factories and farms. In more than 150 countries, we have strong, long-standing relationships with customers who know us for our powerful combination of leading product brands and applications expertise, backed by a legacy of innovation.

For more information on how Xylem can help you, go to www.xyleminc.com



UNITED STATES

100 Cummings Center Dr. 17942 Cowan
 Suite 535-N Irvine, CA 92614
 Beverly, MA 01915 Tel: +1 949 608 3900
 Tel: +1 978 281 0440 Fax: +1 949 608 3888
 Fax: +1 978 283 2619

UNITED KINGDOM

Bingley Road, Hoddesdon Via Tommaseo, 6, 20059
 Hertfordshire EN11 0BU Vimercate, Milano
 Tel: +44 1992 450145 Tel: +39 039 6852323
 Fax: +44 1992 450145 Fax: +39 039 666307

GERMANY

Oststraße 28
 22844 Norderstedt
 Tel: +49 40 53 53 730
 Fax: +49 40 53 53 73 11

CHINA

32/F Tower A, Hongqiao
 City Center of Shanghai
 100 Zunyi Road
 Shanghai 200051
 Tel: +86 21 2208 2888
 Fax: +86 21 2208 2999



ACCURACY AND COMPLETENESS OF INFORMATION

All information in this literature regarding products and services provided by Jabsco is subject to change without prior notice. Reasonable efforts are taken to ensure the accuracy and integrity of all information provided here, but Jabsco is not responsible for misprints, out-of-date information, or errors. Jabsco makes no warranty, express or implied, or assumes any legal liability or responsibility for the accuracy or completeness of any information contained in this literature.

Jabsco is a trademark of Xylem Inc. or one of its subsidiaries.
 © 2016 Xylem, Inc.