

xylem
Let's Solve Water



e-HM™
TAILOR-MADE FOR THE INDUSTRY

 **LOWARA**
a xylem brand

For when a reliable essential.

Temperature control

- Electronic Data Processing
- Laser Equipment
- Industrial Refrigeration
- Heating and Cooling in industrial processes
- Variable speed drives



Food & Beverage

- Liquid Boosting and Transfer
- Mixing/Dosing



Water treatment

- Ultra and nano filtration Systems
- Reverse Osmosis
- Softening, demineralizing and ionizing systems
- Dead end filtration

water supply is



16.000
per hour

Industrial washing & cleaning

- Degreasing and Washing of product equipment
- Washing Machines, including car washing
- Mobile Washing Units
- Cleaning Units



per hour

4.500

Chemical & pharmaceutical industries

- Distilling System
- Evaporation

Here comes the water.

Minimal leakage risk.

The pump body has a maximum of two seal points to minimize the leakage risk.



Supremely efficient.

State-of-the-art hydraulics with best-in-class efficiency. IE3 motors as standard. Can be equipped with Hydrovar pump controller or permanent magnet motor with embedded VFD when a speed control helps save energy.



Tailor-made for your application.

Product range to fit most applications which provides a full range of solutions: our e-HM™ comes in a variety of materials and configurations designed to fulfil all the requirements of the most common systems.



Robust industrial design.

Thick sheet metal in pump body; long lifetime. Special bearing force reduction design for long bearing life. Oversized motors available for high density liquids.



Easy to build in into equipment.

Same distance to suction port on most models.






Flexible solutions.

Compact version for confined spaces. High efficiency version where low energy consumption is a priority.



Extensive range.

			
Model	1	3	5
Flow range (m ³ /h)	0,7÷2,4	1,2÷4,4	2,4÷8,5
Max head (m)	152	159	159
Power (kW)	0,30÷1,5	0,30÷2,2	0,30÷3,0
Max pump efficiency (%)	49	58	69
Max operating pressure (bar)	16	16	16
Temperature range	-30°C - +120°C	-30°C - +120°C	-30°C - +120°C

Tailor-made to your needs.

Material options:

Pump

- AISI 304
- AISI 316
- Electropolished and passivated AISI 316
- Victaulic connections as option

O-rings

- EPDM
- FPM
- Kalrez

Mechanical face seal

- Carbon
- Ceramic
- Silicon carbide

Motor options:

Standard Voltage

50 Hz:

1~: 220-240 V

3~: 220-240/380-415V, up to 3 kW

380-415/660-690V, from 4 kW included

60 Hz

1~: 230V

3~: 220-380V

50/60 Hz

3~: 230-400V 50 Hz / 265-460V 60 Hz

3~: 400-690V 50 Hz / 460V 60 Hz

Multiple Voltage options available

1-2 sizes oversized motors

PTC in windings

Heated motor for chiller applications

Higher ambient temperature

(up to 50°C) for warm environments



10

5÷14

159

0,75÷5,5

71

16

-30°C - +120°C



15

8÷24

102

0,75÷5,5

72

16

-30°C - +120°C



22

11÷29


76

2,2÷5,5

71

16

-30°C - +120°C



Variable-speed drive options.

Xylem variable-speed pump controllers reduce energy consumption up to 70% compared to full speed pump. Complete solution; Hydrovar includes VSD, transmitters and micro processor controller.

Hydrovar (from 1,1 kW).

Fully flexible variable-speed drive with setting options that optimise pump function. Can control up to 8 other pumps. Can control the pump in four different ways:

- Manual stepless speed setting
- Constant pressure
- Constant flow
- Variable pressure according to pump system curve

e-HM smart (up to 2.2KW).

e-HM smart is fitted with high efficient IE5 permanent magnet motors and integrated variable speed drive. A smart, easy-to-set integrated drive can operate in a sensed or sensorless mode in single, twin or multi-pump systems of up to three pumps, with no need for an external control panel or a PLC. The drive also includes BACnet or Modbus and Wi-Fi as an option.

- Works with your system to make it efficient
- Power supply: single phase 50 or 60 Hz



Pump design.

The e-HM is a non-self-priming, end-suction horizontal multistage, high pressure centrifugal pump, with axial threaded inlet and radial threaded outlet.

UL listed version available.

Xylem |'zīləm|

- 1) The tissue in plants that brings water upward from the roots;
- 2) a leading global water technology company.

We're a global team unified in a common purpose: creating advanced technology solutions to the world's water challenges. Developing new technologies that will improve the way water is used, conserved, and re-used in the future is central to our work. Our products and services move, treat, analyze, monitor and return water to the environment, in public utility, industrial, residential and commercial building services settings. Xylem also provides a leading portfolio of smart metering, network technologies and advanced analytics solutions for water, electric and gas utilities. In more than 150 countries, we have strong, long-standing relationships with customers who know us for our powerful combination of leading product brands and applications expertise with a strong focus on developing comprehensive, sustainable solutions.

For more information on how Xylem can help you, go to www.xylem.com



For information and technical support
Xylem Service Italia Srl

Via Dottor Vittorio Lombardi 14
36075 - Montecchio Maggiore (VI) - Italy
Tel. (+39) 0444 707111
Fax (+39) 0444 491043
www.lowara.com
www.xylem.com

Xylem reserves the right to make modification without prior notice.
Lowara, Flygt and Xylem are trademarks of Xylem Inc. or one of its subsidiaries. © 2019 Xylem, Inc.