



Lowara Z6 Borehole Pump

COMBINING QUALITY DESIGN WITH AUSTRALIAN ASSEMBLY FOR FAST DELIVERY



The Lowara Z6 borehole pump range epitomises design and efficiency for peak below ground performance. Its full stainless steel construction, including precision cast discharge head and motor support, enables reliability and long service life. This has led to the Lowara Z6 pumps being well established in Australia & New Zealand for over 25 years.


The Lowara Z6 is now locally assembled providing faster and more efficient service.

The addition of Australian assembly enables prompt delivery and an improved customer experience, whilst maintaining the same level of quality that you have come to expect from Xylem.

Features include:

- Capacities up to 78m³/h
- Head up to 700m
- Assembled in Australia
- Available in AISI 304 (Z6) or AISI 316 (ZN6)

Z6 Series Operating Characteristics at 50Hz



Z6 Series Construction

The cutaway diagram illustrates the internal components of the Z6 Series pump, including the motor adapter, shaft, bearings, impeller, and pump bowl. Callout boxes provide the following details:

- Precision cast head provides high protection against water hammer and ensures a rigid and safe connection to the delivery pipe.**
- Tungsten carbide bearings ensures proper shaft alignment in the worst conditions.**
- Modular design with limited parts allows for simpler maintenance.**
- Improved design of the shaft grooves allows for easy and fast disassembly.**
- Removable coupling for easy repair and disassembly.**
- Stainless steel motor adapter to ensure a rigid connection of the pump to the motor. Available for 4", 6" and 8" motor connections.**
- Safety hook for easy connection to a safety rope.**
- Safety screws to lock the delivery pipe.**
- Integrated non return valve.**
- Integrated up thrust bearing.**
- Suction part of the impeller fitted with removable wear ring for low cost maintenance.**
- Pump shaft fitted with stainless steel spacers for improved protection.**
- Straps designed to be resistant to the maximum pump pressure.**
- Pump bowl made out of one single piece without external welding for improved resistance to the well environment and to the pump pressure.**

Australia
Tel: 1800 Lowara
Email: solve@xylem.com
www.xylem.com/au

New Zealand
Tel: 0800 33 19 14
Email: solve@xylem.com
www.xylem.com/nz

xylem
Let's Solve Water